# **Product datasheet**

Specifications





# EVlink Wallbox - 3.7 kW - T2 socket outlet with shutter - charging station

EVH2S3P04K

### Main

| Range                     | EVlink                        |
|---------------------------|-------------------------------|
| Product Name              | EVlink Wallbox                |
| Product Or Component Type | Charging station              |
| Device Short Name         | EVH2                          |
| Poles Description         | 1P + N                        |
| Mounting Mode             | Wall-mounted                  |
| Offer Type                | Standard                      |
| Max Power                 | 3.7 kW 16 A                   |
| Number Of Charge Point    | 1                             |
| Connection To The Vehicle | Socket-outlet T2 with shutter |
| Access Control System     | Key                           |

## Complementary

| Rated Supply Voltage   | 220240 V AC 50/60 Hz                            |
|------------------------|-------------------------------------------------|
| Earthing System        | П                                               |
|                        | TN                                              |
| Number Of Inputs       | 1                                               |
| Input Type             | Contact for power limitation                    |
|                        | Contact for delayed charging                    |
| Control Type           | 1 white button, function: stop/restart          |
|                        | 1 green button, function: cable unlocking       |
| Local Signalling       | 1 multi-colour LED, function: status indication |
| Height                 | 480 mm                                          |
| Width                  | 331.5 mm                                        |
| Depth                  | 170 mm                                          |
| Net Weight             | 5.6 kg                                          |
| Colour                 | White (RAL 9003)                                |
|                        | Grey (RAL 7016)                                 |
| Standards              | IEC 61851-1                                     |
|                        | IEC 62196-2                                     |
|                        | IEC 61851-22                                    |
|                        | IEC 62196-1                                     |
| Product Certifications | CE                                              |
|                        | CB                                              |

## **Environment**

| Ip Degree Of Protection               | IP54 conforming to IEC 60529 |
|---------------------------------------|------------------------------|
| Ik Degree Of Protection               | IK10 conforming to IEC 62262 |
| Ambient Air Temperature For Operation | -3050 °C                     |
| Ambient Air Temperature For Storage   | -4080 °C                     |
| Relative Humidity                     | 595 %                        |

# **Packing Units**

| _                            |           |
|------------------------------|-----------|
| Unit Type Of Package 1       | PCE       |
| Number Of Units In Package 1 | 1         |
| Package 1 Height             | 26.000 cm |
| Package 1 Width              | 53.200 cm |
| Package 1 Length             | 40.000 cm |
| Package 1 Weight             | 7.789 kg  |
| Unit Type Of Package 2       | P06       |
| Number Of Units In Package 2 | 4         |
| Package 2 Height             | 50.000 cm |
| Package 2 Width              | 60.000 cm |
| Package 2 Length             | 80.000 cm |
| Package 2 Weight             | 40.980 kg |



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration                                                                                   |
|--------------------------|-----------------------------------------------------------------------------------------------------|
| Eu Rohs Directive        | Compliant with Exemptions                                                                           |
| China Rohs Regulation    | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile                                                                       |
| Circularity Profile      | End of Life Information                                                                             |