



W300 ADJUSTABLE MODULAR DEVICE RAIL PRISMA G

03011

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Rail
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G duct
Type Of Rail	Adjustable Modular
Installed Device	TeSys: fixed GV2L TeSys: fixed GV2P TeSys: fixed GV3 ComPact: fixed NG160 without earth leakage protection - control: toggle ComPact: fixed NG160 NA without earth leakage protection - control: toggle Altistart: ATS01N103/106FT TeSys: fixed D or K contactors <= 40 A - horizontal installation TeSys: fixed GV2 + D or K contactors <= 40 A - horizontal installation TeSys: fixed GV3Pxx1 + LC1D40 to D65 - horizontal installation TeSys: fixed TeSys U - horizontal installation ComPact: fixed NSXm without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSXm with earth leakage protection - control: toggle - vertical installation
Poles Description	1 x 3P: fixed NG160 1 x 4P: fixed NG160 1 x 3P: fixed NG160 NA 1 x 4P: fixed NG160 NA 4 x 4P: fixed NG160 NA 4 x 4P: fixed D or K contactors <= 40 A horizontal installation 4 x 3P: fixed GV2 + D or K contactors <= 40 A horizontal installation 4 x 3P: fixed GV2L 4 x 3P: fixed GV2P 3 x 3P: fixed GV3P 3 x 3P: fixed GV3Pxx1 + LC1D40 to D65 horizontal installation 4 x 3P: fixed TeSys U horizontal installation 1 x 3P or 4P: fixed NSXm vertical installation

Complementary

Installation Description

Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm

Number Of Vertical Modules [50 Mm]

- 4 module(s): ATS01N103/106FT in 300 mm Widefloor-standing duct
- 4 module(s): ATS01N103/106FT in 300 mm Widewall-mounted duct
- 3 module(s): D or K contactors <= 40 A, direct in 300 mm Widefloor-standing duct
- 3 module(s): D or K contactors <= 40 A, direct in 300 mm Widewall-mounted duct 5 module(s): GV2 + D or K contactors <= 40 A, direct in 300 mm Widefloor-standing
- 5 module(s): GV2 + D or K contactors <= 40 A, direct in 300 mm Widewall-mounted duct
- 3 module(s): GV2L, direct in 300 mm Widefloor-standing duct
- 3 module(s): GV2L, direct in 300 mm Widewall-mounted duct
- 3 module(s): GV2P, direct in 300 mm Widefloor-standing duct
- 3 module(s): GV2P, direct in 300 mm Widewall-mounted duct
- 5 module(s): GV3, direct in 300 mm Widefloor-standing duct
- 5 module(s): GV3, direct in 300 mm Widewall-mounted duct
- 7 module(s): GV3Pxx1 + LC1D40 to D65, direct in 300 mm Widefloor-standing duct
- 7 module(s): GV3Pxx1 + LC1D40 to D65, direct in 300 mm Widewall-mounted duct
- $5\ \text{module(s)}\xspace$ NG160 without earth leakage protection , direct in 300 mm Widefloor-standing duct
- 5 module(s): NG160 without earth leakage protection , direct in 300 mm Widewall-mounted duct
- $5\ \text{module(s)}\xspace$ NG160 NA without earth leakage protection , direct in 300 mm Widefloor-standing duct
- $5\ \text{module(s)}\xspace$ NG160 NA without earth leakage protection , direct in 300 mm Widewall-mounted duct
- 7 module(s): NSXm without earth leakage protection , direct in 300 mm Widefloor-standing duct
- 7 module(s): NSXm without earth leakage protection , direct in 300 mm Widewall-mounted duct
- $7\ \text{module(s):}\ \text{NSXm}$ without earth leakage protection , connection block in 300 mm Widefloor-standing duct
- $7\ \text{module(s):}\ NSXm$ without earth leakage protection , connection block in 300 mm Widewall-mounted duct
- 5 module(s): TeSys U, direct in 300 mm Widefloor-standing duct
- 5 module(s): TeSys U, direct in 300 mm Widewall-mounted duct
- 4 module(s): TeSys U, direct in 300 mm Widefloor-standing duct
- 4 module(s): TeSys U, direct in 300 mm Widewall-mounted duct
- $7\ \text{module(s):}\ \text{NSXm}$ with earth leakage protection , direct in 300 mm Widefloor-standing duct
- 7 $\operatorname{module}(s)$: NSXm with earth leakage protection , direct in 300 mm Widewall-mounted duct
- 7 module(s): NSXm with earth leakage protection , connection block in 300 mm Widefloor-standing duct
- 7 module(s): NSXm with earth leakage protection , connection block in 300 mm Widewall-mounted duct

9 Mm Pitches	20	
Quantity Per Set	Set of 1	
Height	58 mm	
Width	217 mm	
Depth	97 mm	
Net Weight	0.18 kg	
Colour	Natural	
Material	Metal	

Environment

Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.5 cm
Package 1 Width	5.7 cm

Package 1 Length	22 cm
Package 1 Weight	260 g

Contractual warranty

Warranty 12 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
②	Rohs Exemption Information Yes
Ø	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile