


Product datasheet

Specifications



FRONT PLATE NSX/CVS630 VERTICAL TOGGLE/ROTARY HANDLE/PLUG-IN WIDTH 600/650 9M

03275

! Discontinued

! Discontinued on: 12 May 2023

Main

Range	Prisma
Range Of Product	Prisma G Prisma P
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P cubicle
Type Of Front Plate	Cut-out
Installed Device	ComPact: fixed NSX400 without earth leakage protection - control: toggle - vertical installation EasyPact: fixed CVS400 without earth leakage protection - control: direct front rotary handle - vertical installation EasyPact: fixed CVS630 without earth leakage protection - control: direct front rotary handle - vertical installation ComPact: fixed NSX400 without earth leakage protection - control: direct front rotary handle - vertical installation ComPact: plug-in NSX400 without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX400 without earth leakage protection - control: motor mechanism - vertical installation ComPact: plug-in NSX400 without earth leakage protection - control: direct front rotary handle - vertical installation ComPact: plug-in NSX400 without earth leakage protection - control: motor mechanism - vertical installation ComPact: drawout NSX400 without earth leakage protection - control: toggle - vertical installation ComPact: drawout NSX400 without earth leakage protection - control: direct front rotary handle - vertical installation ComPact: drawout NSX400 without earth leakage protection - control: motor mechanism - vertical installation ComPact: fixed NSX630 without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX630 without earth leakage protection - control: direct front rotary handle - vertical installation ComPact: plug-in NSX630 without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX630 without earth leakage protection - control: motor mechanism - vertical installation ComPact: plug-in NSX630 without earth leakage protection - control: direct front rotary handle - vertical installation ComPact: plug-in NSX630 without earth leakage protection - control: motor mechanism - vertical installation ComPact: drawout NSX630 without earth leakage protection - control: toggle - vertical installation ComPact: drawout NSX630 without earth leakage protection - control: direct front rotary handle - vertical installation ComPact: drawout NSX630 without earth leakage protection - control: motor mechanism - vertical installation

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Poles Description	1 x 4P: mounting plate support: NSX400 vertical installation 1 x 3P: mounting plate support: CVS400 vertical installation 1 x 4P: mounting plate support: CVS400 vertical installation 1 x 3P: mounting plate support: CVS630 vertical installation 1 x 4P: mounting plate support: CVS630 vertical installation 1 x 3P: mounting plate support: NSX400 vertical installation 1 x 3P: mounting plate support: NSX630 vertical installation 1 x 4P: mounting plate support: NSX630 vertical installation
Operating Position	Vertical

Complementary

Enclosure/Cubicle Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm
Connection Position	Linery FC Direct connection
Number Of Vertical Modules [50 Mm]	9
Standards	IEC 61439-1 IEC 61439-2
Product Certifications	ASEFA
Material	Steel
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	450 mm
Width	500 mm
Net Weight	1.72 kg
Quantity Per Set	Set of 1

Functional Unit	600 mm Prisma G floor-standing enclosure ComPact NSX400 without fixed toggle vertical 4P 1 direct
	600 mm Prisma G wall-mounted enclosure ComPact NSX400 without fixed toggle vertical 4P 1 direct
	650 mm 400 mm Prisma P cubicle EasyPact CVS400 without fixed direct front rotary handle vertical 3P 1 direct 13
	650 mm 400 mm Prisma P cubicle EasyPact CVS400 without fixed direct front rotary handle vertical 4P 1 direct 13
	650 mm 400 mm Prisma P cubicle EasyPact CVS630 without fixed direct front rotary handle vertical 3P 1 direct 13
	650 mm 400 mm Prisma P cubicle EasyPact CVS630 without fixed direct front rotary handle vertical 4P 1 direct 13
	650 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed toggle vertical 3P 1 direct 11
	650 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed toggle vertical 4P 1 direct 11
	650 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in toggle vertical 3P 1 direct 11
	650 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in toggle vertical 4P 1 direct 11
	650 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed direct front rotary handle vertical 3P 1 direct 11
	650 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed direct front rotary handle vertical 4P 1 direct 11
	650 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed motor mechanism vertical 3P 1 direct 11
	650 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed motor mechanism vertical 4P 1 direct 11
	650 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in direct front rotary handle vertical 3P 1 direct 11
	650 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in direct front rotary handle vertical 4P 1 direct 11
	650 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in motor mechanism vertical 3P 1 direct 11
	650 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in motor mechanism vertical 4P 1 direct 11
	650 mm 400 mm Prisma P cubicle ComPact NSX400 without drawout toggle vertical 3P 1 direct 11
	650 mm 400 mm Prisma P cubicle ComPact NSX400 without drawout toggle vertical 4P 1 direct 11
	650 mm 400 mm Prisma P cubicle ComPact NSX400 without drawout direct front rotary handle vertical 3P 1 direct 11
	650 mm 400 mm Prisma P cubicle ComPact NSX400 without drawout direct front rotary handle vertical 4P 1 direct 11
	650 mm 400 mm Prisma P cubicle ComPact NSX400 without drawout motor mechanism vertical 3P 1 direct 11
	650 mm 400 mm Prisma P cubicle ComPact NSX400 without drawout motor mechanism vertical 4P 1 direct 11
	650 mm 400 mm Prisma P cubicle ComPact NSX630 without fixed toggle vertical 3P 1 direct 13
	650 mm 400 mm Prisma P cubicle ComPact NSX630 without fixed toggle vertical 4P 1 direct 13
	650 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in toggle vertical 3P 1 direct 13
	650 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in toggle vertical 4P 1 direct 13
	650 mm 400 mm Prisma P cubicle ComPact NSX630 without fixed direct front rotary handle vertical 3P 1 direct 13
	650 mm 400 mm Prisma P cubicle ComPact NSX630 without fixed direct front rotary handle vertical 4P 1 direct 13
	650 mm 400 mm Prisma P cubicle ComPact NSX630 without fixed motor mechanism vertical 3P 1 direct 13
	650 mm 400 mm Prisma P cubicle ComPact NSX630 without fixed motor mechanism vertical 4P 1 direct 13
	650 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in direct front rotary handle vertical 3P 1 direct 13
	650 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in direct front rotary handle vertical 4P 1 direct 13
	650 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in motor mechanism vertical 3P 1 direct 13
	650 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in motor mechanism vertical 4P 1 direct 13
	650 mm 400 mm Prisma P cubicle ComPact NSX630 without drawout toggle vertical 3P 1 direct 13
	650 mm 400 mm Prisma P cubicle ComPact NSX630 without drawout toggle vertical 4P 1 direct 13
	650 mm 400 mm Prisma P cubicle ComPact NSX630 without drawout direct front rotary handle vertical 3P 1 direct 13
	650 mm 400 mm Prisma P cubicle ComPact NSX630 without drawout direct front rotary handle vertical 4P 1 direct 13

650 mm 400 mm Prisma P cubicle ComPact NSX630 without drawout motor
mechanism vertical 3P 1 direct 13

650 mm 400 mm Prisma P cubicle ComPact NSX630 without drawout motor
mechanism vertical 4P 1 direct 13

600 mm Prisma G floor-standing enclosure EasyPact CVS400 without fixed direct
front rotary handle vertical 3P 1 direct with long terminal shield 15

600 mm Prisma G wall-mounted enclosure EasyPact CVS400 without fixed direct
front rotary handle vertical 3P 1 direct with long terminal shield 15

600 mm Prisma G floor-standing enclosure EasyPact CVS400 without fixed direct
front rotary handle vertical 4P 1 direct with long terminal shield 15

600 mm Prisma G wall-mounted enclosure EasyPact CVS400 without fixed direct
front rotary handle vertical 4P 1 direct with long terminal shield 15

600 mm Prisma G floor-standing enclosure EasyPact CVS630 without fixed direct
front rotary handle vertical 3P 1 direct with long terminal shield 15

600 mm Prisma G wall-mounted enclosure EasyPact CVS630 without fixed direct
front rotary handle vertical 3P 1 direct with long terminal shield 15

600 mm Prisma G floor-standing enclosure EasyPact CVS630 without fixed direct
front rotary handle vertical 4P 1 direct with long terminal shield 15

600 mm Prisma G wall-mounted enclosure EasyPact CVS630 without fixed direct
front rotary handle vertical 4P 1 direct with long terminal shield 15

600 mm Prisma G floor-standing enclosure ComPact NSX400 without fixed toggle
vertical 3P 1 direct with long terminal shield 12

600 mm Prisma G wall-mounted enclosure ComPact NSX400 without fixed toggle
vertical 3P 1 direct with long terminal shield 12

600 mm Prisma G floor-standing enclosure ComPact NSX400 without fixed toggle
vertical 4P 1 direct with long terminal shield 12

600 mm Prisma G wall-mounted enclosure ComPact NSX400 without fixed toggle
vertical 4P 1 direct with long terminal shield 12

600 mm Prisma G floor-standing enclosure ComPact NSX400 without fixed direct
front rotary handle vertical 3P 1 direct with long terminal shield 15

600 mm Prisma G wall-mounted enclosure ComPact NSX400 without fixed direct
front rotary handle vertical 3P 1 direct with long terminal shield 15

600 mm Prisma G floor-standing enclosure ComPact NSX400 without fixed direct
front rotary handle vertical 4P 1 direct with long terminal shield 15

600 mm Prisma G wall-mounted enclosure ComPact NSX400 without fixed direct
front rotary handle vertical 4P 1 direct with long terminal shield 15

600 mm Prisma G floor-standing enclosure ComPact NSX630 without fixed toggle
vertical 3P 1 direct with long terminal shield 13

600 mm Prisma G wall-mounted enclosure ComPact NSX630 without fixed toggle
vertical 3P 1 direct with long terminal shield 13

600 mm Prisma G floor-standing enclosure ComPact NSX630 without fixed toggle
vertical 4P 1 direct with long terminal shield 13

600 mm Prisma G wall-mounted enclosure ComPact NSX630 without fixed toggle
vertical 4P 1 direct with long terminal shield 13

600 mm Prisma G floor-standing enclosure ComPact NSX630 without fixed direct
front rotary handle vertical 3P 1 direct with long terminal shield 15

600 mm Prisma G wall-mounted enclosure ComPact NSX630 without fixed direct
front rotary handle vertical 3P 1 direct with long terminal shield 15

600 mm Prisma G floor-standing enclosure ComPact NSX630 without fixed direct
front rotary handle vertical 4P 1 direct with long terminal shield 15

600 mm Prisma G wall-mounted enclosure ComPact NSX630 without fixed direct
front rotary handle vertical 4P 1 direct with long terminal shield 15

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	46.0 cm
Package 1 Length	51.0 cm
Package 1 Weight	1.7 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	11.0 cm
Package 2 Width	52.5 cm
Package 2 Length	53.0 cm
Package 2 Weight	10.55 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	60
Package 3 Height	80.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	117.5 kg

Contractual warranty

Warranty	12 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile