

Product datasheet

Specifications



Exclusive - ceiling rose - 150 W - white

GROC

⚠ Discontinued on: 24 Nov 2023

⚠ To be discontinued

Main

Range Of Product	Exclusive
Product Or Component Type	Ceiling rose
Device Presentation	Complete product
Colour Tint	White Base: clear
Quantity Per Set	Set of 10

Complementary

Device Mounting	Ceiling
Fixing Mode	By screws
Current Consumption	6 A
Rated Lamp Wattage	150 W
Material	Urea (carbamide) PC (polycarbonate): base
Type Of Installation	Indoor
Height	88 mm
Length	88 mm
Width	32 mm
Net Weight	0.077 kg

Environment

Standards	BS 67 BS EN 61184
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	9 cm
Package 1 Length	9 cm
Package 1 Weight	73.8 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	14 cm
Package 2 Length	18.6 cm
Package 2 Weight	818 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	200
Package 3 Height	30 cm
Package 3 Width	39.2 cm
Package 3 Length	50 cm
Package 3 Weight	17.055 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

<div><div><div>✓</div></div></div> <div>Rohs Exemption Information</div>	<div>Yes</div>
<hr/>	
Eu Rohs Directive	Compliant with Exemptions
<hr/>	
China Rohs Regulation	<div><div>China RoHS declaration</div><div>Product out of China RoHS scope. Substance declaration for your information</div></div>
<hr/>	
Environmental Disclosure	<div>Product Environmental Profile</div>
<hr/>	
Circularity Profile	No need of specific recycling operations
<hr/>	