Product datasheet

Specifications





Switch disconnector fuse, TeSys GS, 3P, 32A, fuse type BS

GS1DDB3

- ! Discontinued on: 15 Feb 2024
- ! To be end-of-service on: 15 Feb 2025

① Discontinued

Main

Range	TeSys
Product Name	TeSys GS
Device Short Name	GS1 DD
Product Or Component Type	Switch-disconnector-fuse
Device Application	Protection
Design	Compact
Poles Description	3P
Protected Poles Description	3t
Contacts Type And Composition	3 NO
[Ith] Conventional Free Air Thermal Current	32 A (at 40 °C)
[le] Rated Operational Current	20 A at 440 V 2 poles in series per phase DC-23A 20 A at 440 V 2 poles in series per phase DC-23B 32 A at 400690 V AC-23A 32 A at 400690 V AC-23B
Fuse Type	BS
Fuse Size	A1
Network Type	DC AC
Network Frequency	50/60 Hz

Complementary

Type Of Operating Handle	External frontal External left side External right side Direct frontal
Mounting Support	Plate Rail
[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
Rated Operational Power In W	15 kW at 400 V 25 kW at 690 V
Making Capacity	320 A at 400 V AC-23B
[Icm] Rated Short-Circuit Making Capacity	80 kA at 400 V with protection by gG fuses
Breaking Capacity	256 A at 400 V (AC-23B)

19 Apr 2024 Life Is On Schneider



Short-Circuit Withstand	5.5 kA	
Mechanical Durability	20000 cycles	
Electrical Durability	1500 cycles AC-23A	
	1500 cycles AC-23B	
	300 cycles DC-23A	
	300 cycles DC-23B	
Connections - Terminals	Power circuit: screw-clamp terminals2.516 mm² flexible	
Tightening Torque	Power circuit: 3 N.m - on screw-clamp terminals	

Environment

Standards	IEC 60947-3	
Product Certifications	CE	
Protective Treatment	тн	
Ip Degree Of Protection	IP20 conforming to IEC 60529 (with terminal cover)	
Ambient Air Temperature For Operation	-2070 °C	
Ambient Air Temperature For Storage	-4080 °C	
Fire Resistance	960 °C body conforming to IEC 60695-2-1	
Height	98 mm	
Width	96 mm	
Depth	112 mm	
Net Weight	0.5 kg	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	10.3 cm
Package 1 Length	11.7 cm
Package 1 Weight	503.0 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	4
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	2.218 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information