


Product datasheet

Specifications



W650 ADJUSTABLE MODULAR DEVICE RAIL PRISMA P



03402

Main

Range	Prisma
Range of product	Prisma P
Product or component type	Rail
Accessory / separate part category	Installation accessory
Range compatibility	Prisma P
Type of rail	Adjustable Modular
Installed device	TeSys: fixed GV2L TeSys: fixed GV2P TeSys: fixed GV3 ComPact: fixed NG160 without earth leakage protection - control: toggle ComPact: fixed NG160 NA without earth leakage protection - control: toggle ComPact: fixed NG160 with earth leakage protection - control: toggle Altistart: ATS01N Altistart: ATS01N103/106FT TeSys: fixed D or K contactors <= 40 A - horizontal installation TeSys: fixed GV2 + D or K contactors <= 40 A - horizontal installation TeSys: fixed TeSys U - horizontal installation PowerLogic: PM5500 PowerLogic: iEM3000 PowerLogic: PM3000 PowerLogic: PM5563RD ComPact: fixed NSXm without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSXm with earth leakage protection - control: toggle - vertical installation
Poles description	9 x 3P: fixed GV2L 9 x 3P: fixed GV2P 7 x 3P: fixed GV3 1 x 3P: fixed NG160 1 x 4P: fixed NG160 1 x 3P: fixed NG160 NA 1 x 4P: fixed NG160 NA 9 x 4P: fixed D or K contactors <= 40 A horizontal installation 9 x 3P: fixed GV2 + D or K contactors <= 40 A horizontal installation 9 x 3P: fixed TeSys U horizontal installation 1 x 3P or 4P: fixed NSXm vertical installation

Complementary

Installation description	Cubicle - width 650 mm depth 400 mm
Enclosure nominal height	2000 mm
Number of vertical modules [50 mm]	5 module(s): ATS01N in 650 mm Widecubicle 6 module(s): ATS01N in 650 mm Widecubicle 4 module(s): ATS01N103/106FT in 650 mm Widecubicle 3 module(s): D or K contactors <= 40 A, direct in 650 mm Widecubicle 5 module(s): GV2 + D or K contactors <= 40 A, direct in 650 mm Widecubicle 3 module(s): GV2L, direct in 650 mm Widecubicle 3 module(s): GV2P, direct in 650 mm Widecubicle 5 module(s): GV3, direct in 650 mm Widecubicle 4 module(s): iEM3000 in 650 mm Widecubicle

5 module(s): NG160 without earth leakage protection , direct in 650 mm Widecubicle
 5 module(s): NG160 NA without earth leakage protection , direct in 650 mm Widecubicle
 8 module(s): NSXm without earth leakage protection , direct in 650 mm Widecubicle
 4 module(s): PM3000 in 650 mm Widecubicle
 3 module(s): PM5500 in 650 mm Widecubicle
 3 module(s): PM5563RD in 650 mm Widecubicle
 5 module(s): TeSys U, direct in 650 mm Widecubicle
 4 module(s): TeSys U, direct in 650 mm Widecubicle
 5 module(s): NG160 with earth leakage protection , direct in 650 mm Widecubicle
 8 module(s): NSXm with earth leakage protection , direct in 650 mm Widecubicle

9 mm pitches	48
Quantity per set	Set of 1
Height	30 mm
Width	563 mm
Depth	325 mm
Net weight	0.86 kg
Colour	Natural
Material	Metal

Environment

Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASEFA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	850 g
Package 1 Height	3 cm
Package 1 width	5 cm
Package 1 Length	52 cm
Unit Type of Package 2	S04
Number of Units in Package 2	20
Package 2 Weight	17.9 kg
Package 2 Height	30 cm
Package 2 width	40 cm
Package 2 Length	60 cm
Unit Type of Package 3	P12
Number of Units in Package 3	160
Package 3 Weight	147.04 kg
Package 3 Height	75 cm
Package 3 width	80 cm
Package 3 Length	120 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration

Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	12 months
-----------------	-----------