Product datasheet

Specifications





Auxiliary contact, TeSys GS, 1 C/ O, 3P, 1250A, fuse type DIN, size 4, for GS1 GS2 Blown fuse

GS2AF73

() Discontinued on: 9 Feb 2023

(!) Discontinued

Main

Range Of Product	TeSys	
Device Short Name	GS2AF	
Product Or Component Type	Auxiliary contact	
Contact Application	Blown fuse signalling	
Contacts Type And Composition	1 C/O	
Contact Operation	Instantaneous	
[Ith] Conventional Free Air Thermal Current	16 A (at 40 °C)	
[le] Rated Operational Current	12 A at 24 V DC-13 2 A at 48 V DC-13 3 A at 400 V AC-15 4 A at 230 V AC-15 0.4 A at 220 V DC-13 0.6 A at 110 V DC-13	

Complementary

S fuse-switch disconnector	
y 30000 cycles AC-15	
mpatibility GS	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	10.0 cm
Package 1 Length	20.5 cm
Package 1 Weight	38.0 g

Unit Type Of Package 2	S01
Number Of Units In Package 2	10
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	578.0 g

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information