



switch-disconnector Compact INS250 - 250 A - 3 poles

31106

Main

| wain | | |
|--|---|--|
| Range | ComPact | |
| Product Or Component Type | Switch disconnector | |
| Product Name | ComPacT INS | |
| Poles Description | 3P | |
| Network Type | DC AC | |
| Network Frequency | 50/60 Hz | |
| [le] Rated Operational Current | AC-22A: 250 A AC 50/60 Hz 220/240 V AC-22A: 250 A AC 50/60 Hz 380/415 V AC-22A: 250 A AC 50/60 Hz 440/480 V AC-22A: 250 A AC 50/60 Hz 480 V NEMA AC-22A: 250 A AC 50/60 Hz 500/525 V AC-22A: 250 A AC 50/60 Hz 660/690 V AC-23A: 250 A AC 50/60 Hz 220/240 V AC-23A: 250 A AC 50/60 Hz 380/415 V AC-23A: 250 A AC 50/60 Hz 380/415 V AC-23A: 250 A AC 50/60 Hz 440/480 V AC-23A: 250 A AC 50/60 Hz 480 V NEMA AC-23A: 250 A AC 50/60 Hz 660/690 V DC-22A: 250 A AC 50/60 Hz 500/525 V AC-23A: 250 A AC 50/60 Hz 500/525 V AC-23A: 250 A AC 50/60 Hz 660/690 V DC-22A: 250 A DC 125 V 2 poles in series DC-23A: 250 A DC 125 V 2 poles in series | |
| [Ui] Rated Insulation Voltage | 750 V AC 50/60 Hz | |
| [Ith] Conventional Free Air Thermal Current | 250 A at 60 °C | |
| [Icm] Rated Short-Circuit Making Capacity | 30 kA switch-disconnector alone 690 V AC at 50/60 Hz 330 kA with upstream protection circuit breaker 690 V AC at 50/60 Hz | |
| [Ue] Rated Operational Voltage | 125 V DC 690 V AC 50/60 Hz | |
| Suitability For Isolation | Yes | |
| Contact Position Indicator | Yes | |
| Visible Break | No | |
| Pollution Degree | 3 | |

Complementary

| Control Type | Direct front rotary handle |
|-------------------|----------------------------|
| Handle Colour | Black |
| Mounting Mode | Fixed |
| Mounting Support | Rail Plate |
| Upside Connection | Front |

| Downside Connection | Front |
|----------------------------------|--|
| Maximum Power | AC-23: 132 kW at 380/415 V AC 50/60 Hz |
| | AC-23: 150 kW at 440 V AC 50/60 Hz |
| | AC-23: 150 kW at 480 V AC 50/60 Hz (NEMA) |
| | AC-23: 160 kW at 500/525 V AC 50/60 Hz |
| | AC-23: 210 kW at 660/690 V AC 50/60 Hz |
| | AC-23: 75 kW at 220/240 V AC 50/60 Hz |
| | AC-23: 75 kW at 230 V AC 50/60 Hz (NEMA) |
| Rated Duty | Uninterrupted |
| [Icw] Rated Short-Time Withstand | 1.8 kA during 30 s conforming to IEC 60947-3 |
| Current | 2.2 kA during 20 s conforming to IEC 60947-3 |
| | 4.9 kA during 3 s conforming to IEC 60947-3 |
| | 8.5 kA during 1 s conforming to IEC 60947-3 |
| Mechanical Durability | 15000 cycles |
| Electrical Durability | AC-22A: 1500 cycles 440 V AC 50/60 Hz |
| | AC-22A: 1500 cycles 500 V AC 50/60 Hz |
| | AC-22A: 1500 cycles 690 V AC 50/60 Hz |
| | AC-23A: 1500 cycles 440 V AC 50/60 Hz |
| | AC-23A: 1500 cycles 500 V AC 50/60 Hz |
| | AC-23A: 1500 cycles 690 V AC 50/60 Hz |
| | DC-22A: 1500 cycles 125 V DC 2 poles in series |
| | DC-23A: 1500 cycles 125 V DC 2 poles in series |
| Connection Pitch | 35 mm |
| Height | 136 mm |
| Width | 140 mm |
| Depth | 96 mm |
| Net Weight | 2 kg |
| Environment | |
| | |
| Standards | IEC 60947-3 |

| Standards | IEC 60947-3 IEC 60947-1 | |
|---------------------------------------|------------------------------|--|
| Product Certifications | KEMA-KEUR CCC | |
| Ip Degree Of Protection | IP40 conforming to IEC 60529 | |
| Ik Degree Of Protection | IK07 conforming to EN 50102 | |
| Ambient Air Temperature For Operation | -2570 °C | |
| Ambient Air Temperature For Storage | -5085 °C | |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 13.800 cm |
| Package 1 Width | 16.200 cm |
| Package 1 Length | 17.400 cm |
| Package 1 Weight | 2.216 kg |
| Unit Type Of Package 2 | S04 |
| Number Of Units In Package 2 | 9 |
| Package 2 Height | 30.000 cm |
| Package 2 Width | 40.000 cm |
| Package 2 Length | 60.000 cm |

| Package 2 Weight | 20.710 kg |
|------------------------------|------------|
| Unit Type Of Package 3 | P12 |
| Number Of Units In Package 3 | 36 |
| Package 3 Height | 50.000 cm |
| Package 3 Width | 80.000 cm |
| Package 3 Length | 120.000 cm |
| Package 3 Weight | 92.712 kg |

Contractual warranty

Warranty 12 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |

25 Apr 2024