



switch-disconnector Compact INS320 - 320 A - 3 poles

31108

Main

Main		
Range	ComPact	
Product Or Component Type	Switch disconnector	
Product Name	ComPacT INS	
Poles Description	3P	
Network Type	DC	
	AC	
Network Frequency	50/60 Hz	
[le] Rated Operational Current	AC-22A: 320 A AC 50/60 Hz 220/240 V AC-22A: 320 A AC 50/60 Hz 380/415 V AC-22A: 320 A AC 50/60 Hz 440/480 V AC-22A: 320 A AC 50/60 Hz 480 V NEMA AC-22A: 320 A AC 50/60 Hz 500/525 V AC-22A: 320 A AC 50/60 Hz 660/690 V AC-23A: 320 A AC 50/60 Hz 220/240 V AC-23A: 320 A AC 50/60 Hz 380/415 V AC-23A: 320 A AC 50/60 Hz 440/480 V AC-23A: 320 A AC 50/60 Hz 480 V NEMA AC-23A: 320 A AC 50/60 Hz 660/690 V AC-23A: 320 A AC 50/60 Hz 660/690 V AC-23A: 320 A AC 50/60 Hz 500/525 V AC-23A: 320 A AC 50/60 Hz 500/525 V AC-23A: 320 A AC 50/60 Hz 660/690 V DC-22A: 320 A DC 125 V 2 poles in series DC-23A: 320 A DC 125 V 2 poles in series	
[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz	
[Uimp] Rated Impulse Withstand Voltage	8 kV 8 kV conforming to IEC 60947-3	
[Ith] Conventional Free Air Thermal Current	320 A at 60 °C	
[Icm] Rated Short-Circuit Making Capacity	330 kA with upstream protection circuit breaker 690 V AC at 50/60 Hz 50 kA switch-disconnector alone 690 V AC at 50/60 Hz	
[Ue] Rated Operational Voltage	125 V DC 690 V AC 50/60 Hz	
Suitability For Isolation	Yes	
Contact Position Indicator	Yes	
Visible Break	No	
Pollution Degree	3	

Complementary

Control Type	Direct front rotary handle	
Handle Colour	Black	
Mounting Mode	Fixed	
Mounting Support	Plate Rail	

Upside Connection	Front
Downside Connection	Front
Maximum Power	AC-23: 160 kW at 380/415 V AC 50/60 Hz AC-23: 185 kW at 440 V AC 50/60 Hz
	AC-23: 185 kW at 480 V AC 50/60 Hz (NEMA)
	AC-23: 220 kW at 500/525 V AC 50/60 Hz
	AC-23: 250 kW at 660/690 V AC 50/60 Hz
	AC-23: 90 kW at 220/240 V AC 50/60 Hz
	AC-23: 90 kW at 230 V AC 50/60 Hz (NEMA)
Rated Duty	Uninterrupted
[Icw] Rated Short-Time Withstand	11.5 kA during 3 s conforming to IEC 60947-3
Current	20 kA during 1 s conforming to IEC 60947-3
	4 kA during 30 s conforming to IEC 60947-3
	4.9 kA during 20 s conforming to IEC 60947-3
Mechanical Durability	10000 cycles
Electrical Durability	AC-22A: 1500 cycles 440 V AC 50/60 Hz
	AC-22A: 1500 cycles 500 V AC 50/60 Hz
	AC-22A: 1500 cycles 690 V AC 50/60 Hz
	AC-23A: 1500 cycles 440 V AC 50/60 Hz
	AC-23A: 1500 cycles 500 V AC 50/60 Hz
	AC-23A: 1500 cycles 690 V AC 50/60 Hz
	DC-23A: 1000 cycles 125 V DC 2 poles in series
Connection Pitch	45 mm
Height	205 mm
Width	185 mm
Depth	130 mm
Net Weight	4.6 kg

Environment

Standards	IEC 60947-1 IEC 60947-3	
Product Certifications	CCC KEMA-KEUR	
Ip Degree Of Protection	IP40 conforming to IEC 60529	
Ik Degree Of Protection	IK07 conforming to EN 50102	
Ambient Air Temperature For Operation	-2570 °C	
Ambient Air Temperature For Storage	-5085 °C	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.500 cm
Package 1 Width	19.000 cm
Package 1 Length	22.500 cm
Package 1 Weight	5.012 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	4
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm

Package 2 Length	60.000 cm	
Package 2 Weight	20.718 kg	
Unit Type Of Package 3	P12	
Number Of Units In Package 3	16	
Package 3 Height	50.000 cm	
Package 3 Width	80.000 cm	
Package 3 Length	120.000 cm	
Package 3 Weight	91.936 kg	

Contractual warranty

Warranty 12 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information