Product datasheet





Add-on contact block, TeSys Deca Frame 2/3,1NO+1NO(fault),front,spring terminal, for GV2/GV3 (except GV3ME)

GVAED1013

① To be discontinued

Discontinued on: 24 Oct 2020

Main

Range	TeSys TeSys Deca
Device Short Name	GVAED
Product Or Component Type	Auxiliary contact block
Product Compatibility	GV3L GV3P
Mounting Location	Front side
Auxiliary Contacts Operation	Fault signal 1 NO
Pole Contact Composition	2 NO
Quantity Per Set	Set of 1

Complementary

[Ui] Rated Insulation Voltage	600 V conforming to UL 508 690 V conforming to IEC 60947-1 600 V conforming to CSA C22.2 No 14
[Ue] Rated Operational Voltage	24240 V AC 2460 V DC
[Ith] Conventional Free Air Thermal Current	2.5 A
Mechanical Durability	100000 cycles
Minimum Switching Current	5 mA
Minimum Switching Voltage	17 V
Protection Type	GB2CB circuit breaker GG fuse 10 A
Rated Operational Power In Va	300 VA at 48 V AC-15 - electrical durability: 100000 cycles 400 VA at 690 V AC-15 - electrical durability: 100000 cycles 500 VA at 110127 V AC-15 - electrical durability: 100000 cycles 500 VA at 500 V AC-15 - electrical durability: 100000 cycles 650 VA at 440 V AC-15 - electrical durability: 100000 cycles 720 VA at 230240 V AC-15 - electrical durability: 100000 cycles 850 VA at 380415 V AC-15 - electrical durability: 100000 cycles
Rated Operational Power In W	120 W at 240 V DC-13 - electrical durability: 100000 cycles 140 W at 110 V DC-13 - electrical durability: 100000 cycles 140 W at 24 V DC-13 - electrical durability: 100000 cycles 180 W at 60 V DC-13 - electrical durability: 100000 cycles 240 W at 48 V DC-13 - electrical durability: 100000 cycles
Height	13 mm

Life Is On Schneider 23 Apr 2024



Width	44.5 mm
Depth	31.5 mm
Net Weight	0.05 kg
Colour	Dark grev

Environment

Environmental Characteristic	Normal environment
Product Certifications	UKCA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.5 cm
Package 1 Width	4.5 cm
Package 1 Length	3.0 cm
Package 1 Weight	20.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	6.5 cm
Package 2 Width	7.5 cm
Package 2 Length	12.0 cm
Package 2 Weight	205.0 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	220
Package 3 Height	15.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	4.965 kg

Contractual warranty

Warranty	18 months	



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
②	Mercury Free	
	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information