



# circuit breaker Compact NS800L - Micrologic 5.0 - 800 A - 4 poles 4t

33557

! Discontinued on: 31 Mar 2024

! To be discontinued

#### Main

Mani		
Range	ComPact	
Product Name	ComPact NS	
Range Of Product	ComPact NS630b1600	
Device Short Name	Compact NS800L	
Product Or Component Type	Circuit breaker	
Device Application	Distribution	
Number Of Poles	4P	
Protected Poles Description	4D	
Neutral Position	Left	
(In) Rated Current Up To 65 °C	800 A at 50 °C	
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz	
Network Type	AC	
Network Frequency	50/60 Hz	
Suitability For Isolation	Yes conforming to EN/IEC 60947-2	
Utilisation Category	Category A	
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	130 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 150 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 150 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 100 kA Icu at 500/525 V AC 50/60 Hz conforming to IEC 60947-2	
Performance Level	L 150 kA 415 V AC	
Trip Unit Name	MicroLogic 5.0	
Trip Unit Technology	Electronic	
Trip Unit Protection Functions	LSI	
Control Type	Rotary handle Toggle	
Circuit Breaker Mounting Mode	Fixed	

## Complementary

[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2

[Ics] Rated Service Short-Circuit Breaking Capacity	100 kA at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 130 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 150 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 150 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical Durability	10000 cycles
Electrical Durability	2000 cycles at 690 V In 3000 cycles at 690 V In/2 3000 cycles at 440 V In 4000 cycles at 440 V In/2
Power Losses	20 W
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connection Pitch	70 mm
Protection Type	L : for overload protection (long time) S : for short time short-circuit protection I : for instantaneous short-circuit protection
Trip Unit Rating	800 A at 50 °C
Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable 9 settings
[Ir] Long-Time Protection Pick-Up Adjustment Range	0.41 x ln
Long-Time Protection Delay Adjustment Type Tr	Adjustable 9 settings
[Tr] Long-Time Protection Delay Adjustment Range	12.5600 s at 1.5 x lr 0.524 s at 6 x lr 0.716.6 s at 7.2 x lr
Thermal Memory	20 mn
Short-Time Protection Pick-Up Adjustment Type Isd	Adjustable 9 settings
[Isd] Short-Time Protection Pick- Up Adjustment Range	1.510 x lr
Short-Time Protection Delay Adjustment Type Tsd	Adjustable
[Tsd] Short-Time Protection Delay Adjustment Range	0.10.4 s l²t=on 00.4 s l²t=off
Instantaneous Protection Pick-Up Adjustment Type Ii	Adjustable
[li] Instantaneous Protection Pick- Up Adjustment Range	Off 215 x ln
Earth-Leakage Protection	Without
Neutral Protection Settings	No protection (3D) 0.5 x lr (3D + N/2) 1 x lr (4D)
Zone Selective Interlocking Zsi	Without
Auxiliary Contact Composition	1 NO/NC
Local Signalling	4 LEDs (red) for fault indication 1 LED (yellow) for overload
Width (W)	280 mm
Height (H)	327 mm
Depth (D)	147 mm
Net Weight	18 kg

## **Environment**

Standards	EN/IEC 60947-2	
Product Certifications	ASEFA ASTA	
Pollution Degree	3 conforming to IEC 60947	
Ip Degree Of Protection	IP40 conforming to IEC 60529	
Ik Degree Of Protection	IK07 conforming to EN 50102	
Ambient Air Temperature For Operation	-2570 °C	
Ambient Air Temperature For Storage	-5085 °C	
Relative Humidity	095 %	
Operating Altitude	02000 m without derating 2000 m5000 m with derating	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	37.0 cm
Package 1 Width	38.0 cm
Package 1 Length	30.0 cm
Package 1 Weight	17.431 kg

## **Contractual warranty**

Warranty 12 months

## Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

25 Apr 2024