Product datasheet

Specification





Acti 9 - Auxiliary contact iOF/ SD+OF - 2OC - AC/DC

A9A26929

- ! Discontinued on: 7 Apr 2024
- ! To be end-of-service on: 1 Jun 2024

(!) Discontinued

Main

Range Of Product	Acti9
Product Or Component Type	Double OC or fault contact
Device Short Name	iOF/SD+OF
Signal Contacts Composition	2 C/O
[In] Rated Current	DC-12 1 A at 130 V, DC
	DC-12 1.5 A at 60 V, DC
	DC-12 2 A at 48 V, DC
	DC-12 6 A at 24 V, DC
	AC-12 3 A at 415 V, AC 50/60 Hz
	AC-12 6 A at 240 V, AC 50/60 Hz
9 Mm Pitches	1

Complementary

[Ui] Rated Insulation Voltage	500 V
[Uimp] Rated Impulse Withstand Voltage	4 kV
Local Signalling	Mechanical indicator
Mounting Mode	Fixed
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	NO
Height	90 mm
Width	9 mm
Depth	73 mm
Net Weight	43 g
Colour	White
Connections - Terminals	Screw clamp terminal (top and bottom) 2 cable(s) 2.5 mm² - rigid Screw clamp terminal (top and bottom) 2 cable(s) 1.5 mm² - flexible with ferrule Screw clamp terminal (top and bottom) 1 cable(s) 0.52.5 mm² - flexible Screw clamp terminal (top and bottom) 1 cable(s) 14 mm² - rigid
Wire Stripping Length	10 mm
Tightening Torque	1 N.m

Environment

Standards	EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1

Ambient Air Temperature For Operation	-3570 °C
Ambient Air Temperature For Storage	-4085 °C

Packing Units

PCE
1
7.500 cm
2.400 cm
9.200 cm
50.000 g
BB1
12
8.500 cm
10.000 cm
27.000 cm
693.000 g
S03
120
30.000 cm
30.000 cm
40.000 cm
7.600 kg

Contractual warranty

Warranty 12 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
②	Mercury Free	
	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information