

Product datasheet

Specifications



Auxiliary contact block, TeSys K,
2NC, front mounting, spring
terminals, EN 50012

LA1KN023M

! Discontinued

Main

Range	TeSys
Product Name	TeSys K
Product Or Component Type	Auxiliary contact block
Device Short Name	LA1
Product Compatibility	3P contactor
Range Compatibility	TeSys K LC1K
Mounting Location	Front
Pole Contact Composition	2 NC
Contacts Operation	Instantaneous
[Ue] Rated Operational Voltage	690 V AC 25...400 Hz
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947-5-1 600 V conforming to UL 60947-5-1 600 V conforming to CSA C22.2 No 60947-5-1
[Ith] Conventional Free Air Thermal Current	10 A (at 50 °C)
Standards	EN/IEC 60947-5-1 UL 60947-5-1 CSA C22.2 No 60947-5-1 GB/T 14048.5 JIS C8201-5-1
Product Certifications	CB Scheme CCC UL CSA CE UKCA

Complementary

Irms Rated Making Capacity	110 A at <= 690 V AC conforming to IEC 60947
Permissible Short-Time Rating	80 A 1 s 60 A 500 ms 110 A 100 ms
Associated Fuse Rating	10 A gG at <= 690 V conforming to IEC 60947
Minimum Switching Current	5 mA
Minimum Switching Voltage	17 V
Non Overlap Distance	0.5 mm
Insulation Resistance	> 10 MOhm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - Terminals	Spring terminals 1 cable(s) 0.75...1.5 mm²flexible without cable end Spring terminals 1 cable(s) 0.75...1.5 mm²rigid
Height	30 mm
Width	38 mm
Depth	35 mm
Net Weight	0.045 kg

Environment

Environmental Characteristic	Normal environment
Ip Degree Of Protection	IP20 conforming to IEC 60529
Protective Treatment	TC conforming to IEC 60068
Ambient Air Temperature For Storage	-50...80 °C
Ambient Air Temperature For Operation	-25...50 °C
Operating Altitude	2000 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1