Product datasheet

Specifications





Contactor, Tesys Deca, railway S207, 3P(3NO), AC-3/AC-3e, 9A, <=440V, 72V DC low consumption coil, lugs-ring terminals

LC1D096SLS207

() Discontinued

() Discontinued on: 9 Feb 2023

Main

Man	
Range	TeSys TeSys Deca
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Resistive load Motor control
Utilisation Category	AC-3 AC-1 AC-3e
Poles Description	3P
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz
[Ie] Rated Operational Current	9 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 25 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 9 A (at <60 °C) at <= 440 V AC AC-3e for power circuit

Complementary

Motor Power Kw	2.2 kW at 220/230 V AC 50 Hz (AC-3)	
	4 kW at 380/400 V AC 50 Hz (AC-3)	
	4 kW at 415 V AC 50 Hz (AC-3)	
	4 kW at 440 V AC 50 Hz (AC-3)	
	5.5 kW at 500 V AC 50 Hz (AC-3)	
	5.5 kW at 660/690 V AC 50 Hz (AC-3)	
	2.2 kW at 220/230 V AC 50 Hz (AC-3e)	
	4 kW at 380/400 V AC 50 Hz (AC-3e)	
	4 kW at 415 V AC 50 Hz (AC-3e)	
	4 kW at 440 V AC 50 Hz (AC-3e)	
	5.5 kW at 500 V AC 50 Hz (AC-3e)	
	5.5 kW at 660/690 V AC 50 Hz (AC-3e)	
Pole Contact Composition	3 NO	
Protective Cover	With	
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1	
Auxiliary Contact Composition	1 NO + 1 NC	
[Ui] Rated Insulation Voltage	Power circuit: 690 V conforming to IEC 60947-4-1	
	Signalling circuit: 690 V conforming to IEC 60947-1	
[Uimp] Rated Impulse Withstand	6 kV conforming to IEC 60947	
Voltage	-	
Overvoltage Category	III	

[Ith] Conventional Free Air Thermal Current	10 A (at 60 °C) for signalling circuit 25 A (at 60 °C) for power circuit
Irms Rated Making Capacity	250 A at 440 V for power circuit conforming to IEC 60947 140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1
Rated Breaking Capacity	250 A at 440 V for power circuit conforming to IEC 60947
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 25 A gG at <= 690 V coordination type 1 for power circuit 20 A gG at <= 690 V coordination type 2 for power circuit
Time Constant	37 ms
Control Circuit Type	DC low consumption
Coil Technology	With integral suppression device
Control Circuit Voltage Limits	0.10.25 Uc (-4070 °C):drop-out DC 0.71.25 Uc (-4070 °C):operational DC
Average Impedance	2.5 mOhm - Ith 25 A 50 Hz for power circuit
Power Dissipation Per Pole	1.56 W AC-1 0.2 W AC-3 0.2 W AC-3e
Minimum Switching Current	5 mA for signalling circuit
Minimum Switching Voltage	17 V for signalling circuit
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
Operating Time	77 ±15 % ms closing 25 ±20 % ms opening
Maximum Operating Rate	3600 cyc/h 60 °C
nrush Power In W	4 W (at 20 °C)
Hold-In Power Consumption In W	4 W at 20 °C
Insulation Resistance	> 10 MOhm for signalling circuit
Connections - Terminals	Control circuit: lugs-ring terminals - external diameter: 8 mm Power circuit: lugs-ring terminals - external diameter: 9.5 mm
Tightening Torque	Control circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver flat Ø 6 mm M3.5 Control circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver Philips No 2 M3.5 Power circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver Philips No 2 M3.5 Power circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver flat Ø 6 mm M3.5 Control circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver pozidriv No 2 M3.5 Power circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver pozidriv No 2 M3.5
Mounting Support	Rail Plate
Electrical Durability	0.6 Mcycles 25 A AC-1 at Ue <= 440 V 2 Mcycles 9 A AC-3 at Ue <= 440 V 2 Mcycles 9 A AC-3e at Ue <= 440 V
Mechanical Durability	30 Mcycles
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Operating Altitude	03000 m
Compatibility Code	LC1D
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 EN 45545: R22 HL3 EN 45545: R26 HL3 DIN 5510-2

IEC CCC EAC UA TR UKCA

Environment

Climatic Withstand	conforming to IACS E10 conforming to IEC 60947-1 Annex Q category D
Ambient Air Temperature For Storage	-6080 °C
Fire Resistance	850 °C conforming to IEC 60695-2-1
Height	77 mm
Width	45 mm
Depth	95 mm
Net Weight	0.32 kg
Mechanical Robustness	Vibrations contactor open (2 Gn, 5300 Hz) Vibrations contactor closed (4 Gn, 5300 Hz) Shocks contactor open (10 Gn for 11 ms) Shocks contactor closed (15 Gn for 11 ms)

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.6 cm
Package 1 Width	9.4 cm
Package 1 Length	5.4 cm
Package 1 Weight	556.0 g
Unit Type Of Package 2	\$02
Number Of Units In Package 2	15
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	8.72 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	240
Package 3 Height	77.0 cm
Package 3 Width	80.0 cm
Package 3 Length	60.0 cm
Package 3 Weight	148.74 kg

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations