

Product datasheet

Specifications



TeSys GV2 - Enclosure for TeSys GV2ME - IP41

GV2MC01

Main

Range	TeSys
Product Or Component Type	Enclosure
Device Short Name	GV2MC
Accessory / Separate Part Category	Mounting accessory
Product Compatibility	GV2ME
Enclosure Type	Surface mounting

Complementary

Auxiliary Mounting Location	Left Right
Height	147 mm
Width	93 mm
Depth	84 mm

Environment

Ip Degree Of Protection	IP41
Environmental Characteristic	Standard environment

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10 cm
Package 1 Width	10 cm
Package 1 Length	15.2 cm
Package 1 Weight	263 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	27
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	8.258 kg
Unit Type Of Package 3	P06

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 3	108
Package 3 Height	80 cm
Package 3 Width	80 cm
Package 3 Length	60 cm
Package 3 Weight	41.912 kg

Contractual warranty

Warranty	12 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



RoHS/REACH

Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations