# **Product datasheet**

Specification





## servo motor MH3 100 5,8Nm,no key,multi,no brake,IP65/ IP67,4kRPM

MH31002P02A2200

### Main

Range Compatibility	PacDrive 3
Product Or Component Type	AC servo motors
Device Short Name	MH3

## **Complementary**

Complementary	
Maximum Mechanical Speed	6000 rpm
[Us] Rated Supply Voltage	115480 V
Network Number Of Phases	Three phase
Continuous Stall Current	5.04 A
Continuous Stall Torque	6 N.m, 115480 V, three phase
Continuous Power	2270 W
Peak Stall Torque	18 N.m, 115480 V, three phase
Nominal Output Power	0.59 W, 115 V 1.12 W, 230 V 1.95 W, 400 V 2.27 W, 480 V
Nominal Torque	5.67 N.m for LXM52 at 4.81 mA, 115 V, 1 phase 5.33 N.m for LXM52 at 4.58 mA, 230 V, 1 phase 4.67 N.m for LXM52 at 4.1 mA, 400 V, 3 phases 4.2 N.m for LXM52 at 3.73 mA, 480 V, 3 phases 5.67 N.m for LXM62 at 4.81 mA, 115 V, 1 phase 5.33 N.m for LXM62 at 4.58 mA, 230 V, 1 phase 4.67 N.m for LXM62 at 4.1 mA, 400 V, 3 phases 4.2 N.m for LXM62 at 3.73 mA, 480 V, 3 phases
Nominal Speed	1000 rpm for LXM52 at 4.81 mA, 115 V, 1 phase 2000 rpm for LXM52 at 4.58 mA, 230 V, 1 phase 4000 rpm for LXM52 at 4.1 mA, 400 V, 3 phases 5000 rpm for LXM52 at 3.73 mA, 480 V, 3 phases 1000 rpm for LXM62 at 4.81 mA, 115 V, 1 phase 2000 rpm for LXM62 at 4.58 mA, 230 V, 1 phase 4000 rpm for LXM62 at 4.1 mA, 400 V, 3 phases 5000 rpm for LXM62 at 3.73 mA, 480 V, 3 phases
Maximum Current Irms	17.4 A
Shaft End	Smooth shaft
Second Shaft	Without second shaft end
Shaft Diameter	19 mm
Shaft Length	40 mm
Ip Degree Of Protection	IP65 standard
Encoder Type	Multiturn SinCos Hiperface
Speed Feedback Resolution	128 periods

Holding Brake	Without
Mounting Support	International standard flange
Motor Flange Size	100 mm
Electrical Connection	Rotatable right-angled connectors
Torque Constant	1.19 N.m/A at 120 °C
Back Emf Constant	78 V/krpm
Number Of Motor Poles	10
Rotor Inertia	6.28 kg.cm²
Stator Resistance	1.97 Ohm
Stator Inductance	8.24 mH
Stator Electrical Time Constant	5 ms
Maximum Radial Force Fr	990 N at 1000 rpm 790 N at 2000 rpm 690 N at 3000 rpm 620 N at 4000 rpm 580 N at 5000 rpm
Type Of Cooling	Natural convection
Length	160.6 mm
Centring Collar Diameter	95 mm
Centring Collar Depth	3.5 mm
Number Of Mounting Holes	4
Mounting Holes Diameter	9 mm
Circle Diameter Of The Mounting Holes	115 mm
Net Weight	4.92 kg

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.0 cm
Package 1 Width	18.0 cm
Package 1 Length	35.6 cm
Package 1 Weight	5.62 kg



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



#### **Certifications & Standards**

Circularity Profile	No need of specific recycling operations
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
<b>Environmental Disclosure</b>	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Reach Regulation	REACh Declaration