# **Product datasheet**

Specification





# TeSys K contactor - 3P - AC-3 <= 440 V 6 A - 1 NC aux. - 230 V AC coil

LC1K0601P7

#### Main

Range	TeSys
Product Or Component Type	Contactor
Device Short Name	LC1K
Device Application	Control
Contactor Application	Motor control

#### Complementary

Complementary	
Utilisation Category	AC-3 AC-3e AC-4
Poles Description	3P
Power Pole Contact Composition	3 NO
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC <= 400 Hz Signalling circuit: <= 690 V AC <= 400 Hz
[le] Rated Operational Current	6 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 6 A (at <60 °C) at <= 440 V AC AC-3e for power circuit
Control Circuit Type	AC at 50/60 Hz
[Uc] Control Circuit Voltage	230 V AC 50/60 Hz
Motor Power Kw	1.5 kW at 220230 V AC 50/60 Hz AC-3 2.2 kW at 380415 V AC 50/60 Hz AC-3 3 kW at 440/690 V AC 50/60 Hz AC-3 1.5 kW at 220230 V AC 50/60 Hz AC-3e 2.2 kW at 380415 V AC 50/60 Hz AC-3e 3 kW at 440/690 V AC 50/60 Hz AC-3e 1.5 kW at 220230 V AC 50/60 Hz AC-3e 3 kW at 380415 V AC 50/60 Hz AC-4 2.2 kW at 380415 V AC 50/60 Hz AC-4 3 kW at 440/690 V AC 50/60 Hz AC-4
Auxiliary Contact Composition	1 NC
[Uimp] Rated Impulse Withstand Voltage	8 kV
Overvoltage Category	Ш
[Ith] Conventional Free Air Thermal Current	20 A (at 60 °C) for power circuit 10 A (at 50 °C) for signalling circuit
Irms Rated Making Capacity	110 A AC for power circuit conforming to IEC 60947 110 A AC for signalling circuit conforming to IEC 60947
Rated Breaking Capacity	110 A at 220230 V conforming to IEC 60947 110 A at 380400 V conforming to IEC 60947 110 A at 415 V conforming to IEC 60947 110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 70 A at 660690 V conforming to IEC 60947

23 Apr 2024 Life Is On Schneider

[Icw] Rated Short-Time Withstand Current	90 A 50 °C - 1 s for power circuit
	85 A 50 °C - 5 s for power circuit 80 A 50 °C - 10 s for power circuit
	60 A 50 °C - 30 s for power circuit
	45 A 50 °C - 1 min for power circuit
	40 A 50 °C - 3 min for power circuit
	20 A 50 °C - >= 15 min for power circuit
	80 A - 1 s for signalling circuit
	90 A - 500 ms for signalling circuit
	110 A - 100 ms for signalling circuit
Associated Fuse Rating	25 A gG at <= 440 V for power circuit
	25 A aM for power circuit
	10 A gG for signalling circuit conforming to IEC 60947
	10 A gG for signalling circuit conforming to VDE 0660
Average Impedance	3 mOhm - Ith 20 A 50 Hz for power circuit
[Ui] Rated Insulation Voltage	Power circuit: 600 V conforming to UL 508
	Power circuit: 690 V conforming to IEC 60947-4-1
	Signalling circuit: 690 V conforming to IEC 60947-4-1
	Signalling circuit: 690 V conforming to IEC 60947-5-1
	Signalling circuit: 600 V conforming to UL 508
	Power circuit: 600 V conforming to CSA C22.2 No 14
	Signalling circuit: 600 V conforming to CSA C22.2 No 14
Insulation Resistance	> 10 MOhm for signalling circuit
Inrush Power In Va	30 VA (at 20 °C)
Hold-In Power Consumption In Va	4.5 VA (at 20 °C)
Heat Dissipation	1.3 W
Control Circuit Voltage Limits	Operational: 0.81.15 Uc (at <50 °C) Drop-out: >= 0.20 Uc (at <50 °C)
Connections - Terminals	Screw clamp terminals 1 cable(s) 1.54 mm²solid
	Screw clamp terminals 1 cable(s) 0.754 mm²flexible without cable end
	Screw clamp terminals 1 cable(s) 0.342.5 mm²flexible with cable end
	Screw clamp terminals 2 cable(s) 1.54 mm²solid
	Screw clamp terminals 2 cable(s) 0.754 mm²flexible without cable end
	Screw clamp terminals 2 cable(s) 0.341.5 mm²flexible with cable end
Maximum Operating Rate	3600 cyc/h
Auxiliary Contacts Type	type instantaneous 1 NC
Signalling Circuit Frequency	<= 400 Hz
Minimum Switching Current	5 mA for signalling circuit
Minimum Switching Voltage	17 V for signalling circuit
Mounting Support	Plate Rail
Tightening Torque	0.81.3 N.m - on screw clamp terminals Philips No 2
<b>.</b>	0.81.3 N.m - on screw clamp terminals flat Ø 6 mm
	0.81.3 N.m - on screw clamp terminals pozidriv No 2
Operating Time	1020 ms coil de-energisation and NO opening 1020 ms coil energisation and NO closing
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1
·····•	B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Non Overlap Distance	0.5 mm
Mechanical Durability	10 Mcycles
Electrical Durability	1.3 Mcycles 6 A AC-3 at Ue <= 440 V
	1.3 Mcycles 6 A AC-3e at Ue <= 440 V 0.05 Mcycles 36 A AC-4 at Ue <= 440 V
	• • • • • • • • • • • • • • • • • • •

Mechanical Robustness	Shocks contactor closed, on X axis: 10 Gn for 11 ms conforming to IEC 60068-2-27
	Shocks contactor closed, on Y axis: 15 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed, on Z axis: 15 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on X axis: 6 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on Y axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on Z axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Vibrations contactor closed: 4 Gn, 5300 Hz conforming to IEC 60068-2-6 Vibrations contactor opened: 2 Gn, 5300 Hz conforming to IEC 60068-2-6
Height	58 mm
Width	45 mm
Depth	57 mm
Net Weight	0.18 kg

## **Environment**

EN/IEC 60947-4-1
GB/T 14048.4
UL 60947-4-1
CSA C22.2 No 60947-4-1
JIS C8201-4-1
CB Scheme
CCC
UL
CSA
EAC
CE
UKCA
IP2X conforming to VDE 0106
TC conforming to IEC 60068
TC conforming to DIN 50016
-5080 °C
2000 m without derating
V1 conforming to UL 94
Requirement 2 conforming to NF F 16-101
Requirement 2 conforming to NF F 16-102

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	6.0 cm
Package 1 Length	6.5 cm
Package 1 Weight	179.3 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	50
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	9.203 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	800
Package 3 Height	75.0 cm

Package 3 Width	80.0 cm
Package 3 Length	60.0 cm
Package 3 Weight	155.248 ka

## **Contractual warranty**

Warranty 12 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes


#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information


**Dimensions Drawings** 

#### **Dimensions**

#### Contactors LC1 K, LP1 K, LP4 K: Mounting on Panel



#### Contactors LC1 K, LP1 K, LP4 K: Mounting on Rail AM1 DP200 or AM1 DE200 (35 mm)




## **Product datasheet**

## LC1K0601P7

Connections and Schema

Wiring

3-Pole Contactors: 3P + N/O



3-Pole Contactors: 3P + N/C

