



circuit breaker Compact NSXm 50A 3P 70kA at 380/415V(IEC) EverLink lug

LV426504

! Discontinued on: 15 Jun 2023

! Discontinued

Main

Mairi	
Range	ComPact
Product Name	ComPact NSXm
Range Of Product	ComPact NSXm
Device Short Name	NSXm 50H
Product Or Component Type	Circuit breaker
Device Application	Protection Distribution
Number Of Poles	3P
Protected Poles Description	3D
[In] Rated Current	50 A at 40 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	100 kA Icu at 220240 V AC 50/60 Hz conforming to IEC 60947-2 70 kA Icu at 380415 V AC 50/60 Hz conforming to IEC 60947-2 65 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 30 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 22 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 10 kA Icu at 600690 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	H 70 kA 415 V AC
Trip Unit Name	TM-D
Trip Unit Technology	Thermal-magnetic
Trip Unit Protection Functions	Ц
Control Type	Toggle
Circuit Breaker Mounting Mode	By screws Clip-on

Complementary

[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV

[Ics] Rated Service Short-Circuit	100 kA at 220240 V AC 50/60 Hz conforming to IEC 60947-2
Breaking Capacity	
2. caning capacity	70 kA at 380415 V AC 50/60 Hz conforming to IEC 60947-2
	65 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2
	30 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2
	22 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2
	2.5 kA at 660690 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical Durability	20000 cycles
Florida d Bonda Who	
Electrical Durability	10000 cycles at 440 V In
	20000 cycles at 440 V In/2
	5000 cycles at 690 V In
	10000 cycles at 690 V In/2
Manustina Compant	
Mounting Support	Plate
	DIN rail
Connection Terminals	1 Everlink lug wire size 2.595 mm², rigid or stranded aluminium/copper
Commodium forminais	
	1 Everlink lug wire size 2.570 mm², flexible copper
Connection Pitch	35 mm with spreaders
	27 mm without spreaders
	27 mm without spreaders
9 Mm Pitches	9 module
Protection Type	L. for example of materials (the man)
Trotection type	L : for overload protection (thermal)
	I : for short-circuit protection (magnetic)
Trip Unit Rating	50 A at 40 °C
Lang Time Diels III. Adjustment	A.P. 4.11
Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable
Type ii (Tileriliai Frotection)	
[Ir] Long-Time Protection Pick-Up Adjustment Range	0.71 x ln
Long-Time Protection Delay	Fixed
Adjustment Type Tr	rixeu
[Im] Magnetic Protection Pick-Up	600 A
Range	000 A
Earth-Leakage Protection	Without
	Without
Number Of Slots For Electrical	1 slot(s) for auxiliary switch OF
Auxiliaries	1 slot(s) for alarm switch SD
	1 slot(s) for voltage release MN or MX
	1 Siot(3) for voltage release with or wix
Width (W)	81 mm
Height (H)	137 mm
Depth (D)	80 mm
Net Weight	1.06 kg
Colour	Grey (RAL 7016)

Environment

Standards	EN/IEC 60947
Product Certifications	CCC EAC Marine
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-5085 °C
Relative Humidity	095 %
Operating Altitude	02000 m without derating 20005000 m with derating

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.5 cm
Package 1 Width	9.0 cm
Package 1 Length	22.0 cm
Package 1 Weight	1.3 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	8
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	12.29 kg

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations