

Product datasheet

Specifications



Control station, plastic, stop function, 1 flush push button, red, 1 NC, ATEX

XAWG110EX

⚠ Discontinued on: 1 Jul 2020

⚠ Discontinued

Main

Range Of Product	Harmony XAW
Product Or Component Type	Complete control station
Device Short Name	XAWG
Control Station Application	Stop function
Material	Glass fibre reinforced
Control Station Composition	1 flush push-button, red, spring return 1 NC

Complementary

Colour Of Base Of Enclosure	Black
Colour Of Cover	Black
Cable Entry	1 entry for ISO M20 cable gland
Width	85 mm
Depth	70 mm
Height	146 mm
Net Weight	0.620 kg
Marking	Ex tb IIIC T85°C Db IP65
Mechanical Durability	5000000 cycles
Short-Circuit Protection	10 A cartridge fuse type gG

[Ie] Rated Operational Current	3 A at 240 V, AC-15, A600 conforming to EN/IEC 60947-5-1 6 A at 120 V, AC-15, A600 conforming to EN/IEC 60947-5-1 0.1 A at 600 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 0.27 A at 250 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 0.55 A at 125 V, DC-13, Q600 conforming to EN/IEC 60947-5-1 1.2 A at 600 V, AC-15, A600 conforming to EN/IEC 60947-5-1
--------------------------------	--

Environment

Ambient Air Temperature For Operation	-20...60 °C
Overvoltage Category	II conforming to IEC 60536
Ip Degree Of Protection	IP65 conforming to IEC 60529

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN 60079-0:2009
	EN 60079-31:2009
	EN 60947-5-4
	EN 61000-6-2
	EN/IEC 60947-1
	EN/IEC 60947-5-1
	IEC 60079-0:2007
	IEC 60079-31:2008
Directives	94/9/EC - ATEX directive
Dust Zone	Zone 21 - 22
Product Certifications	INERIS 04ATEX0023X

Contractual warranty

Warranty	18 months
----------	-----------