# **Product datasheet**

Specifications





# Anti Harmonic detuned reactor 6.5kvar 210Hz (4.2) 5.7% 50Hz 400V

LVR05065A40T

## Main

Range	PowerLogic
Device Short Name	DR
Product Or Component Type	Detuned reactor
Network Frequency	50 Hz
Reactive Power Rating	6.5 kvar for 400 V AC 50 Hz
Network Rated Voltage	400 V AC 50 Hz
Tuning Order	4.2 - 210 Hz - 5.7 % - 50 Hz

# Complementary

Power Losses (Max)	100 W
Value Of Inductance	4.727 mH
Inductance Tolerance	- 5 % to 5 % per phase
Fundamental Current Rating	9.4 A
Rms Current Rating	11.4 A
Electrical Insulation Class	Class H
[Ui] Rated Insulation Voltage	1.1 kV
Dielectric Test Voltage	4 kV 50 Hz 1 minute
[Imp] Maximum Permanent Current	1.3 x l1
Harmonic Current Spectrum	2.9 % x l3 67.8 % x l5 18.6 % x l7 6.2 % x l11
Dynamic Withstand Current	2.2 x lsc
[Ith] Conventional Free Air Thermal Current	2 A at 250 V AC 50 Hz
Type Of Installation	Indoor installation
Type Of Cooling	Forced convection
Connections - Terminals	Pad terminal
Fixing Center	200 x 125 mm
Height	220 mm
Width	240 mm
Depth	160 mm
Net Weight	9 kg

## Environment

Standards	IEC 60068
Ip Degree Of Protection	IP00
Operating Altitude	<= 2000 m
Ambient Air Temperature For Operation	055 °C at <= 1000 m 050 °C at > 10002000 m
Average Ambient Air Temperature For Operation	50 °C at <= 1000 m (average over 24 hours) 40 °C at <= 1000 m (average over 1 year) 45 °C at > 10002000 m (average over 24 hours) 35 °C at > 10002000 m (average over 1 year)
Climatic Withstand	Relative humidity: 2080 % Salt mist (400 V/50 Hz) : 250 hours

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	22.5 cm
Package 1 Width	28 cm
Package 1 Length	30 cm
Package 1 Weight	9.5 kg

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc

Rohs Exemption Information Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations