Product datasheet

Specification





Discrete I/O module, Modicon TM3, 8 IO (4 inputs, 4 relay outputs, screw) 24 VDC

TM3DM8R

Main

Range Of Product	Modicon TM3
Product Or Component Type	Discrete I/O module
Range Compatibility	Modicon M241
	Modicon M251
	Modicon M221
	Modicon M262
Discrete Input Number	4 for input conforming to IEC 61131-2 Type 1
Discrete Input Logic	Sink or source (positive/negative)
Discrete Input Voltage	24 V
Discrete Input Current	7 mA for input
Discrete Output Type	Relay normally open
Discrete Output Number	4
Discrete Output Logic	Positive or negative
Discrete Output Voltage	24 V DC for relay output
	240 V AC for relay output
Discrete Output Current	2000 mA for relay output

Complementary

Discrete I/O Number	8
Current Consumption	5 mA at 5 V DC via bus connector (at state off)
	0 mA at 24 V DC via bus connector (at state on)
	0 mA at 24 V DC via bus connector (at state off)
	25 mA at 5 V DC via bus connector (at state on)
Discrete Input Voltage Type	DC
Voltage State 1 Guaranteed	1528.8 V for input
Current State 1 Guaranteed	>= 2.5 mA (input)
Voltage State 0 Guaranteed	05 V for input
Current State 0 Guaranteed	<= 1 mA (input)
Input Impedance	3.4 kOhm
Response Time	4 ms (turn-on)
	4 ms (turn-off)
Maximum Current Per Output Common	7 A
Mechanical Durability	20000000 cycles
Minimum Load	10 mA at 5 V DC for relay output
Local Signalling	1 LED per channel (green) for I/O state

Electrical Connection	$11x2.5~\text{mm}^2$ removable screw terminal block with pitch 5.08 mm adjustment for inputs and outputs
Maximum Cable Distance Between Devices	Unshielded cable: <30 m for regular input
Insulation	Between input and internal logic at 500 V AC Non-insulated between inputs Between input groups and output groups at 1500 V AC Between open contact at 750 V AC Between output and internal logic at 500 V AC Non-insulated between outputs
Marking	CE
Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 rail conforming to IEC 60715 plate or panel with fixing kit
Height	90 mm
Depth	84.6 mm
Width	27.4 mm
Net Weight	0.95 kg

Environment

Product Certifications CULus CE UKCA RCM EAC cULus HazLoc Resistance To Electrostatic Discharge 8 kV in air conforming to IEC 61000-4-2 4 kV on contact conforming to IEC 61000-4-2 Resistance To Electromagnetic 10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3 3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3 1 V/m 2 GHz3 GHz conforming to IEC 61000-4-3 1 V/m 2 GHz3 GHz conforming to IEC 61000-4-3 Resistance To Magnetic Fields 30 A/m 50/60 Hz conforming to IEC 61000-4-8 Resistance To Fast Transients 1 kV for I/O conforming to IEC 61000-4-4 2 kV or relay output conforming to IEC 61000-4-5 1 kV input common mode conforming to IEC 61000-4-5	
Discharge 4 kV on contact conforming to IEC 61000-4-2 Resistance To Electromagnetic Fields 10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3 3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3 1 V/m 2 GHz3 GHz conforming to IEC 61000-4-3 Resistance To Magnetic Fields 30 A/m 50/60 Hz conforming to IEC 61000-4-8 Resistance To Fast Transients 1 kV for I/O conforming to IEC 61000-4-4 2 kV for relay output conforming to IEC 61000-4-4 2 kV output common mode conforming to IEC 61000-4-5	
Fields 3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3 1 V/m 2 GHz3 GHz conforming to IEC 61000-4-3 Resistance To Magnetic Fields 30 A/m 50/60 Hz conforming to IEC 61000-4-8 Resistance To Fast Transients 1 kV for I/O conforming to IEC 61000-4-4 2 kV for relay output conforming to IEC 61000-4-4 Surge Withstand 2 kV output common mode conforming to IEC 61000-4-5	
Resistance To Fast Transients 1 kV for I/O conforming to IEC 61000-4-4 2 kV for relay output conforming to IEC 61000-4-4 Surge Withstand 2 kV output common mode conforming to IEC 61000-4-5	
2 kV for relay output conforming to IEC 61000-4-4 Surge Withstand 2 kV output common mode conforming to IEC 61000-4-5	
·	
,	
Resistance To Conducted Disturbances 10 V 0.1580 MHz conforming to IEC 61000-4-6 3 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) c Marine specification (LR, ABS, DNV, GL)	onforming to
Electromagnetic Emission Radiated emissions - test level: 40 dBμV/m QP class A (10 m) at 30 conforming to IEC 55011 Radiated emissions - test level: 47 dBμV/m QP class A (10 m) at 23 conforming to IEC 55011	
Ambient Air Temperature For Operation -1035 °C vertical installation -1055 °C horizontal installation	
Ambient Air Temperature For -2570 °C Storage	
Relative Humidity 1095 %, without condensation (in operation) 1095 %, without condensation (in storage)	
Ip Degree Of Protection IP20 with protective cover in place	
Pollution Degree 2	
Operating Altitude 02000 m	
Storage Altitude 03000 m	

Vibration Resistance	3.5 mm at 58.4 Hz on DIN rail	
	3 gn at 8.4150 Hz on DIN rail	
	3.5 mm at 58.4 Hz on panel	
	3 gn at 8.4150 Hz on panel	
Shock Resistance	15 an for 11 ms	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	12.5 cm
Package 1 Length	10.5 cm
Package 1 Weight	230.0 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	42
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	10.643 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	504
Package 3 Height	105 cm
Package 3 Width	120 cm
Package 3 Length	80 cm
Package 3 Weight	138 kg



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Dimensions Drawings

Dimensions




(*) 8.5 mm/0.33 in. when the clamp is pulled out.


Product datasheet

TM3DM8R


Mounting and Clearance

Spacing Requirements







Mounting on a Rail



Incorrect Mounting




Mounting on a Panel Surface



(1) Install a mounting strip

Mounting Hole Layout




TM3DM8R

Connections and Schema

Digital Mixed I/O Module (8-channel)

Wiring Diagram (Sink / Source)



- (*) Type T fuse
- (1) The COM0 and COM1 terminals are **not** connected internally.
- (2) To improve the life time of the contacts, and to protect from potential inductive load damage, it is recommended to connect a free wheeling diode in parallel to each inductive DC load or an RC snubber in parallel of each inductive AC load.
- (A) Sink wiring (positive logic)
- (B) Source wiring (negative logic)
- (C) Source wiring (positive logic)
- (D) Sink wiring (negative logic)