

# Product datasheet

Specifications



## LINERGY FC DISTRIBUTION BLOCK FOR COMPACT NSX250 4P FIXED W/O CONNECTION

04408

### Main

Range	Linery
Range of product	Linery
Product or component type	Device feeder
Product name	Linery FC
Accessory / separate part category	Connection accessory
Range compatibility	Prisma P cubicle

### Complementary

Installation description	Cubicle - width 650 mm
Number of devices	3 (4P)
Poles description	4P

### Installed device

ComPact: fixed NSX100...160 without earth leakage protection - control: toggle - vertical installation  
ComPact: fixed NSX250 without earth leakage protection - control: toggle - vertical installation  
ComPact: fixed NSX100...160 with earth leakage protection - control: toggle - vertical installation  
ComPact: fixed NSX250 with earth leakage protection - control: toggle - vertical installation  
ComPact: fixed INS250 - control: direct front rotary handle - vertical installation  
ComPact: fixed INV250 - control: direct front rotary handle - vertical installation  
ComPact: fixed NSX100...160 without earth leakage protection - control: direct front rotary handle - vertical installation  
ComPact: fixed NSX250 without earth leakage protection - control: direct front rotary handle - vertical installation  
ComPact: fixed NSX100...160 without earth leakage protection - control: motor mechanism - vertical installation  
ComPact: fixed NSX250 without earth leakage protection - control: motor mechanism - vertical installation  
ComPact: plug-in NSX100...160 without earth leakage protection - control: direct front rotary handle - vertical installation  
ComPact: plug-in NSX250 without earth leakage protection - control: direct front rotary handle - vertical installation  
ComPact: plug-in NSX100...160 without earth leakage protection - control: motor mechanism - vertical installation  
ComPact: plug-in NSX250 without earth leakage protection - control: motor mechanism - vertical installation  
ComPact: plug-in NSX100...160 without earth leakage protection - control: toggle - vertical installation  
ComPact: plug-in NSX250 without earth leakage protection - control: toggle - vertical installation  
ComPact: fixed NSX100...160 with earth leakage protection - control: direct front rotary handle - vertical installation  
ComPact: fixed NSX250 with earth leakage protection - control: direct front rotary handle - vertical installation  
ComPact: fixed NSX100...160 with earth leakage protection - control: motor mechanism - vertical installation  
ComPact: fixed NSX250 with earth leakage protection - control: motor mechanism - vertical installation  
ComPact: plug-in NSX100...160 with earth leakage protection - control: direct front rotary handle - vertical installation  
ComPact: plug-in NSX250 with earth leakage protection - control: direct front rotary handle - vertical installation  
ComPact: plug-in NSX100...160 with earth leakage protection - control: motor mechanism - vertical installation

ComPact: plug-in NSX250 with earth leakage protection - control: motor mechanism - vertical installation  
 ComPact: plug-in NSX100...160 with earth leakage protection - control: toggle - vertical installation  
 ComPact: plug-in NSX250 with earth leakage protection - control: toggle - vertical installation

<b>Mounting support</b>	Mounting plate
<b>Installation direction</b>	Horizontal
<b>[Ui] rated insulation voltage</b>	750 V AC
<b>[Uimp] rated impulse withstand voltage</b>	8 kV
<b>[Ie] rated operational current</b>	675 A at 40 °C
<b>[Ue] rated operational voltage</b>	690 V
<b>[Ipk] rated peak withstand current</b>	50 kA
<b>I<sup>2</sup>t on activation</b>	25000000 A <sup>2</sup> .s
<b>Permissible current</b>	675 A at 40 °C 615 A at 60 °C 570 A at 70 °C
<b>Connections - terminals</b>	Outgoer: plug in (phase / neutral) , 3 outgoers
<b>Standards</b>	IEC 61439-2 IEC 61439-1
<b>Product certifications</b>	ASEFA KEMA
<b>Quantity per set</b>	Set of 1
<b>Length</b>	440 mm
<b>Height</b>	132 mm
<b>Depth</b>	235 mm
<b>Product weight</b>	8 kg
<b>Colour</b>	Black

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Weight</b>	4.45 kg
<b>Package 1 Height</b>	15 cm
<b>Package 1 width</b>	24 cm
<b>Package 1 Length</b>	46 cm
<b>Unit Type of Package 2</b>	P12
<b>Number of Units in Package 2</b>	42
<b>Package 2 Weight</b>	196.8 kg
<b>Package 2 Height</b>	80 cm
<b>Package 2 width</b>	80 cm
<b>Package 2 Length</b>	120 cm

## Offer Sustainability

<b>Sustainable offer status</b>	Green Premium product
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>REACH free of SVHC</b>	Yes
<b>EU RoHS Directive</b>	Compliant <a href="#">EU RoHS Declaration</a>

<b>Toxic heavy metal free</b>	Yes
<b>Mercury free</b>	Yes
<b>RoHS exemption information</b>	<a href="#">Yes</a>
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>
<b>Circularity Profile</b>	<a href="#">End of Life Information</a>
<b>WEEE</b>	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
<b>Contractual warranty</b>	
<b>Warranty</b>	12 months