# **Product datasheet**

Specification





# Multi 9 - C60 UL1077 - MCB - 4P - 16 A - D Curve - 480Y/277 V - 5 kA

24556

! Discontinued on: 23 Jul 2021

(!) Discontinued

#### Main

Range	Multi9	
Product Name	Multi9 C60	
Product Or Component Type	Miniature circuit-breaker	
Device Short Name	C60 UL1077	
Device Application	Distribution	
Poles Description	4P	
Number Of Protected Poles	4	
Neutral Position	Left	
[In] Rated Current	16 A at 25 °C	
Network Type	AC	
Trip Unit Technology	Thermal-magnetic	
Curve Code	D	
Breaking Capacity	6 kA Icu at 440 V AC conforming to EN/IEC 60947-2 10 kA Icu at 415 V AC conforming to EN/IEC 60947-2 20 kA Icu at 240 V AC conforming to EN/IEC 60947-2 6 kA Icu at 440 V AC conforming to GB 14048.2 10 kA Icu at 415 V AC conforming to GB 14048.2 20 kA Icu at 240 V AC conforming to GB 14048.2 10 kA AIR at 240 V AC conforming to UL 1077 5 kA AIR at 480Y/277 V AC conforming to UL 1077 10 kA AIR at 240 V AC conforming to CSA C22.2 No 235 5 kA AIR at 480Y/277 V AC conforming to CSA C22.2 No 235	
Suitability For Isolation	Yes conforming to EN/IEC 60947-2	

## Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	415 V AC
	240 V AC
	440 V AC
Magnetic Tripping Limit	12 x In +/- 20 % AC
Limitation Class	3 conforming to EN/IEC 60947-2
[Ui] Rated Insulation Voltage	500 V AC conforming to EN/IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to EN/IEC 60947-2
Contact Position Indicator	Yes
Control Type	Toggle

20 Apr 2024 Life Is On Schneider

Local Signalling	ON/OFF indication	
Mounting Mode	Clip-on	
Mounting Support	DIN rail	
9 Mm Pitches	8	
Height	81 mm	
Width	72 mm	
Depth	73 mm	
Net Weight	0.33 kg	
Colour	Grey	
Mechanical Durability	20000 cycles	
Electrical Durability	10000 cycles	
Provision For Padlocking	Padlockable	
Connections - Terminals	rminals Tunnel type terminal (top or bottom)2.525 mm² (AWG 14AWG 4) - rigid	
Wire Stripping Length	14 mm for top or bottom connection	
Tightening Torque	2.5 N.m top or bottom	

### **Environment**

Standards	UL 1077 GB 14048.2 EN/IEC 60947-2 CSA C22.2 No 235	
Product Certifications	UR CSA CCC IEC	
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529	
Pollution Degree	3 conforming to EN/IEC 60947-2	
Overvoltage Category	IV	
Tropicalisation	2 conforming to IEC 60068-1	
Relative Humidity	95 % at 55 °C	
Operating Altitude	2000 m	
Ambient Air Temperature For Operation	-3070 °C	
Ambient Air Temperature For Storage	-4080 °C	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	7.2 cm
Package 1 Length	9 cm
Package 1 Weight	455.467 g

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

#### Well-being performance

	Mercury Free	
	Rohs Exemption Information	Yes
<b>⊘</b>	Halogen Free Product	

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	
Olilla Kolis Kegulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins