



# switch-disconnector Compact INS250 - 100 A - 4 poles

31101

### Main

wan		
Range	ComPact	
Product Or Component Type	Switch disconnector	
Product Name	ComPacT INS	
Poles Description	4P	
Network Type	DC	
	AC	
Network Frequency	50/60 Hz	
[le] Rated Operational Current	AC-22A: 100 A AC 50/60 Hz 220/240 V	
	AC-22A: 100 A AC 50/60 Hz 380/415 V	
	AC-22A: 100 A AC 50/60 Hz 440/480 V	
	AC-22A: 100 A AC 50/60 Hz 480 V NEMA AC-22A: 100 A AC 50/60 Hz 500/525 V	
	AC-22A: 100 A AC 50/60 Hz 500/525 V AC-22A: 100 A AC 50/60 Hz 660/690 V	
	AC-22A: 100 A AC 50/60 Hz 200/690 V AC-23A: 100 A AC 50/60 Hz 220/240 V	
	AC-23A: 100 A AC 50/60 Hz 380/415 V	
	AC-23A: 100 A AC 50/60 Hz 440/480 V	
	AC-23A: 100 A AC 50/60 Hz 480 V NEMA	
	AC-23A: 100 A AC 50/60 Hz 500/525 V	
	AC-23A: 100 A AC 50/60 Hz 660/690 V	
	DC-22A: 100 A DC 125 V 2 poles in series	
	DC-22A: 100 A DC 123 V 2 poles in series	
	DC-23A: 100 A DC 125 V 2 poles in series	
	DC-23A: 100 A DC 250 V 4 poles in series	
[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz	
[Ith] Conventional Free Air Thermal Current	100 A at 60 °C	
[Icm] Rated Short-Circuit Making	30 kA switch-disconnector alone 690 V AC at 50/60 Hz	
Capacity	330 kA with upstream protection circuit breaker 690 V AC at 50/60 Hz	
[Ue] Rated Operational Voltage	250 V DC	
[OC] Nated Operational Voltage	690 V AC 50/60 Hz	
Suitability For Isolation	Yes	
Contact Position Indicator	Yes	
Visible Break	No	
Pollution Degree	3	

## Complementary

Control Type	Direct front rotary handle
Handle Colour	Black
Mounting Mode	Fixed
Mounting Support	Plate
	Rail

Upside Connection  Downside Connection  Maximum Power	Front  Front  AC-23: 22 kW at 220/240 V AC 50/60 Hz  AC-23: 22 kW at 230 V AC 50/60 Hz (NEMA)  AC-23: 45 kW at 380/415 V AC 50/60 Hz
	AC-23: 22 kW at 220/240 V AC 50/60 Hz AC-23: 22 kW at 230 V AC 50/60 Hz (NEMA)
Maximum Power	AC-23: 22 kW at 230 V AC 50/60 Hz (NEMA)
	,
	AC-23: 45 kW at 380/415 V AC 50/60 Hz
	7.6 26. 16 10. 00 007. 16 17.6 60760 1.2
	AC-23: 55 kW at 440 V AC 50/60 Hz
	AC-23: 55 kW at 480 V AC 50/60 Hz (NEMA)
	AC-23: 55 kW at 500/525 V AC 50/60 Hz
	AC-23: 55 kW at 660/690 V AC 50/60 Hz
Rated Duty	Uninterrupted
[Icw] Rated Short-Time Withstand	1.8 kA during 30 s conforming to IEC 60947-3
Current	2.2 kA during 20 s conforming to IEC 60947-3
	4.9 kA during 3 s conforming to IEC 60947-3
	8.5 kA during 1 s conforming to IEC 60947-3
Mechanical Durability	15000 cycles
Electrical Durability	AC-22A: 1500 cycles 440 V AC 50/60 Hz
	AC-22A: 1500 cycles 500 V AC 50/60 Hz
	AC-22A: 1500 cycles 690 V AC 50/60 Hz
	AC-23A: 1500 cycles 440 V AC 50/60 Hz
	AC-23A: 1500 cycles 500 V AC 50/60 Hz
	AC-23A: 1500 cycles 690 V AC 50/60 Hz
	DC-22A: 1500 cycles 250 V DC 4 poles in series
	DC-23A: 1500 cycles 250 V DC 4 poles in series
Connection Pitch	35 mm
Height	136 mm
Width	140 mm
Depth	96 mm
Net Weight	2.2 kg
Environment	
Standards	IEC 60947-1
	IEC 60947-3
Product Certifications	CCC
	KEMA-KEUR
Ip Degree Of Protection	IP40 conforming to IEC 60529
Height Width Depth Net Weight  Environment Standards Product Certifications	35 mm  136 mm  140 mm  96 mm  2.2 kg  IEC 60947-1 IEC 60947-3 CCC KEMA-KEUR

Standards	IEC 60947-1 IEC 60947-3
Product Certifications	CCC KEMA-KEUR
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to EN 50102
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-5085 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.0 cm
Package 1 Width	16.0 cm
Package 1 Length	17.1 cm
Package 1 Weight	2.422 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	9
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm

Package 2 Length	60.0 cm
Package 2 Weight	22.564 kg

# **Contractual warranty**

Warranty 12 months

# Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information