
Product datasheet

Specifications





standard motor mechanism module (MCH), fixed ComPact NS630b to NS1600, 200/250 VDC

33693

Main

Device Short Name	MCH
Product Or Component Type	Motor mechanism
Device Application	Automatic spring charging
Range Compatibility	ComPacT new generation ComPact NS630b1600
Control Type	Standard
[Uc] Control Circuit Voltage	200250 V DC
Circuit Breaker Mounting Mode	Fixed
Circuit Breaker Frame Rated Current	1250 A 1600 A 800 A 1000 A
	630 A

Complementary

Control Signal Type	Maintained Impulse
Circuit Breaker Response Time	60 ms +/- 10 ms open 60 ms +/- 10 ms closed
Maximum Operating Frequency	<= 3 cycles per minute
Maximum Power Consumption In Va	180 VA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.900 cm
Package 1 Width	14.800 cm
Package 1 Length	19.800 cm
Package 1 Weight	1.154 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	20
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	23.500 kg

Unit Type Of Package 3	P12
Number Of Units In Package 3	320
Package 3 Height	90.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	388.000 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information