

Product datasheet

Specifications



Acti 9 time delay iATEt

A9C15419

Main

Range	Acti9
Product Or Component Type	Time delay auxiliary
Device Short Name	iATEt
[Uc] Control Circuit Voltage	24...110 V DC impulse 24...240 V AC 50/60 Hz maintained

Complementary

Type Of Setting	Time delay configuration
Time Delay Range	2 s...10 min 2 s...10 h 6...60 s 1...10 s 6 s...1 h
Maximum Output Current	0.2 A holding 3 A inrush
Hold-In Power Consumption In Va	5 VA
Mounting Mode	Fixed, on the left of TL or CT
Mounting Support	DIN rail
9 Mm Pitches	2
Height	81 mm
Width	18 mm
Depth	60 mm
Colour	White
Overvoltage Category	III
[Uimp] Rated Impulse Withstand Voltage	4 kV
[Ui] Rated Insulation Voltage	440 V
Standards	EN/IEC 60669-2-2
Connections - Terminals	Output connection: yellow clips Input connection: tunnel type terminals 2 cable(s) 2.5 mm² flexible Input connection: tunnel type terminals 2 cable(s) 1.5 mm² rigid
Wire Stripping Length	9 mm
Tightening Torque	0.8 N.m
Range Compatibility	Acti9 Acti9 iCT Acti9 Acti9 iTL
Market Segment	Small commercial Residential

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Compatibility Code	IATeI
--------------------	-------

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529
Ambient Air Temperature For Operation	-20...50 °C
Ambient Air Temperature For Storage	40...80 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	2.3 cm
Package 1 Length	9.0 cm
Package 1 Weight	86.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	108
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	9.789 kg

Contractual warranty

Warranty	12 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Rohs Exemption Information	Yes
 Halogen Free Plastic Parts & Cables Product	
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins