# **Product datasheet**





## circuit breaker Masterpact NW40H10 - 4000 A - 4 poles drawout

48742

### Main

Range	MasterPacT	
Product Name	MasterPact NW	
Circuit Breaker Name	MasterPact NW40H10	
Product Or Component Type	Circuit breaker	
Device Application	Power distribution protection	
Poles Description	4P	
Neutral Position	Left	
Control Unit	Without control unit	
[In] Rated Current	4000 A at 40 °C	
Performance Type	H10 50 kA 1150 V AC	
[Ue] Rated Operational Voltage	1150 V AC 50/60 Hz	
Suitability For Isolation	Yes conforming to EN/IEC 60947-2	
Selectivity Category	Category B	
Control Type	Push-button	
Mounting Mode	Drawout	

### Complementary

[Icu] Rated Ultimate Short-Circuit Breaking Capacity	50 kA at 1150 V AC 50/60 Hz
[Ics] Rated Service Breaking Capacity	50 kA at 1150 V AC 50/60 Hz
[Icw] Rated Short-Time Withstand Current	50 kA 1 s 50 kA 3 s
[Icm] Rated Short-Circuit Making Capacity	105 kA 1150 V AC at 50/60 Hz
Sensor Rating	2000 A 4000 A
[Ui] Rated Insulation Voltage	1250 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	12 kV
Maximum Breaking Time	25 ms
Maximum Closing Response Time	70 ms
Mounting Support	Backplate Rails
Upside Connection	Rear
Downside Connection	Rear

Connection Pitch	150 mm
Mechanical Durability	10000 cycles without maintenance 20000 cycles with maintenance
Electrical Durability	500 cycles 1150 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-2
Height	439 mm
Width	556 mm
Depth	395 mm
Net Weight	120 kg
Standards	EN/IEC 60947-1 EN/IEC 60947-2
Product Certifications	CE CCC EAC

### **Environment**

Ip Degree Of Protection	IP30 conforming to IEC 60529
Pollution Degree	3 conforming to IEC 60664-1
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4085 °C
Operating Altitude	02000 m without derating 2000 m5000 m with derating

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.1 cm
Package 1 Width	0.1 cm
Package 1 Length	0.2 cm
Package 1 Weight	47.0 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >


Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information