# **Product datasheet**

Specification





# iCT 25A 4NO 24V 50Hz contactor

A9C20134

#### Main

Range Of Product	Acti9
Product Name	Acti9 iCT
Product Or Component Type	Contactor
Device Short Name	iCT
Device Application	Motor-heating-lighting
Poles	4P
[le] Rated Operational Current	25 A AC-7A 8.5 A AC-7B
Pole Contact Composition	4 NO
Network Type	AC
Control Type	Remote control
[Uc] Control Circuit Voltage	24 V AC 50 Hz

### Complementary

Network Frequency	50 Hz
[Ue] Rated Operational Voltage	400 V AC 50 Hz
Maximum Power	1.6 W at 400 V AC
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	4 kV
Control Signal Type	Maintained
Switching Frequency	100 switching operations/day
Local Signalling	Action indicator
Hold-In Power Consumption In Va	4.6 VA
Inrush Power In Va	34 VA
Mounting Mode	Clip-on
Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	4
Height	81 mm
Width	36 mm
Depth	60 mm
Colour	White

Mechanical Durability	1000000 cycles
Electrical Durability	100000 cycles IEC/EN 61095 25 A 50 Hz AC-7A
	30000 cycles IEC/EN 61095 8.5 A 50 Hz AC-7B
	30000 cycles IEC/EN 61095 50 Hz AC-7C
	100000 cycles EN/IEC 60947-4-1 50 Hz AC-1
	30000 cycles EN/IEC 60947-4-1 50 Hz AC-3
	30000 cycles EN/IEC 60947-4-1 50 Hz AC-5a
	30000 cycles EN/IEC 60947-4-1 50 Hz AC-5b
Connections - Terminals	Control circuit: tunnel type terminals2 cable(s) 1.5 mm² rigid
	Power circuit: tunnel type terminals1 cable(s) 14 mm² flexible
	Power circuit: tunnel type terminals1 cable(s) 1.56 mm² rigid
	Control circuit: tunnel type terminals1 cable(s) 1.52.5 mm² rigid
	Control circuit: tunnel type terminals2 cable(s) 1.52.5 mm² flexible
Tightening Torque	Control circuit: 0.8 N.m
	Power circuit: 0.8 N.m
Product Compatibility	IACTp
	IACTs
	IACTc
	IATEt
Compatibility Code	ICT
Market Segment	Small commercial
	Residential

#### **Environment**

Standards	IEC/EN 61095
Noise Level	30 dB
Heat Dissipation	1.6 W at 50/60 Hz
Ip Degree Of Protection	IP20
Pollution Degree	2
Tropicalisation	2 conforming to EN 60947-4-1 2 conforming to EN 61095 2 conforming to IEC 1095
Relative Humidity	95 % at 55 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-560 °C
Ambient Air Temperature For Storage	-4070 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	11 cm
Package 1 Length	12.3 cm
Package 1 Weight	234 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	11.5 cm
Package 2 Width	12.5 cm
Package 2 Length	25 cm

Package 2 Weight	1.482 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	36
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	9.37 kg

## **Contractual warranty**

Warranty 18 months

### Sustainability Screen Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

23-Apr-2024