

# Product datasheet

Specifications



## C120N - circuit breaker - 2P - 63A - C curve

A9N18360

### Main

Range Of Product	C120
Range	Acti9
Product Name	C120
Product Or Component Type	Miniature circuit-breaker
Device Short Name	C120N
Device Application	Distribution
Poles Description	2P
Number Of Protected Poles	2
Neutral Position	Left
[In] Rated Current	63 A at 30 °C
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	C
Breaking Capacity	10000 A Icn at 230...400 V AC 50/60 Hz conforming to EN/IEC 60898-1 6 kA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 10 kA Icu at <= 250 V DC conforming to EN/IEC 60947-2 20 kA Icu at 220...240 V AC 50/60 Hz conforming to EN/IEC 60947-2 10 kA Icu at 380...415 V AC 50/60 Hz conforming to EN/IEC 60947-2
Suitability For Isolation	Yes conforming to IEC 60947-2

### Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	380...415 V AC 50/60 Hz 220...240 V AC 50/60 Hz 440 V AC 50/60 Hz <= 250 V DC 230...400 V AC 50/60 Hz
Magnetic Tripping Limit	5...10 x In
[Ics] Rated Service Breaking Capacity	7500 A 75 % conforming to EN/IEC 60898-1 - 230...400 V AC 50/60 Hz 4.5 kA 75 % conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz 7.5 kA 75 % conforming to EN/IEC 60947-2 - 380...415 V AC 50/60 Hz 15 kA 75 % conforming to EN/IEC 60947-2 - 220...240 V AC 50/60 Hz 10 kA 100 % conforming to EN/IEC 60947-2 - <= 250 V DC
Limitation Class	1 conforming to EN/IEC 60947-2
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz conforming to EN/IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to EN/IEC 60947-2
Contact Position Indicator	Yes

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Control Type	Toggle
Local Signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	35 mm symmetrical DIN rail
Comb Busbar And Distribution Block Compatibility	YES
9 Mm Pitches	6
Height	81 mm
Depth	73 mm
Width	54 mm
Net Weight	0.41 kg
Colour	White
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles conforming to IEC 60947-2
Locking Options Description	Handle sealable with cable diameter 0.7mm in OFF or ON position
Connections - Terminals	Tunnel type terminals1...50 mm² rigid Tunnel type terminals1.5...35 mm² flexible
Wire Stripping Length	15 mm
Tightening Torque	3.5 N.m
Earth-Leakage Protection	Separate block

## Environment

Standards	EN/IEC 60898-1 EN/IEC 60947-2
Product Certifications	EAC
Ip Degree Of Protection	IP20 conforming to IEC 60529
Pollution Degree	3 conforming to IEC 60947-2
Overvoltage Category	IV
Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...85 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.3 cm
Package 1 Width	6.8 cm
Package 1 Length	8.4 cm
Package 1 Weight	376 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6

Package 2 Height	8.6 cm
Package 2 Width	9.6 cm
Package 2 Length	33.3 cm
Package 2 Weight	2.328 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	36
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	14.455 kg

## Contractual warranty

Warranty	12 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations