Product datasheet

Specification





Acti 9 xID residual circuit breaker - 63 A - 2P - 30mA class AC instantaneous

A9N16208

Main

Range	Acti9
Product Name	Acti9 xID
Product Or Component Type	Residual current circuit breaker (RCCB)
Device Short Name	xID
Poles Description	2P
Neutral Position	Left
[In] Rated Current	63 A
Network Type	AC
Earth-Leakage Sensitivity	30 mA
Earth-Leakage Protection Time Delay	Instantaneous
Earth-Leakage Protection Class	Type AC
Rated Breaking And Making Capacity	630 A conforming to EN/IEC 61008-1
Suitability For Isolation	Yes

Complementary

Network Frequency	50 Hz
[Ue] Rated Operational Voltage	230240 V AC 50 Hz
[Ui] Rated Insulation Voltage	500 V AC 50 Hz
[Uimp] Rated Impulse Withstand Voltage	6 kV
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	ON, OFF, fault trip
Mounting Mode	Clip-on
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	Downside: biconnect
Connection Pitch	18 mm between phases
9 Mm Pitches	4
Height	81 mm
Width	36 mm
Depth	75 mm
Net Weight	210 g

Colour	White	
Mechanical Durability	4000 cycles	
Electrical Durability	4000 cycles	
Locking Options Description	Padlocking device	
Connections - Terminals	Tunnel type terminals (top or bottom) 135 mm² rigid Tunnel type terminals (top or bottom) 125 mm² flexible	
Wire Stripping Length	14 mm for top or bottom connection	
Tightening Torque	3.5 N.m top or bottom	

Environment

Standards	EN/IEC 61008-1 IEC 61008-2-1 EN 61008-2-1
Product Certifications	ISI
Ip Degree Of Protection	IP20
Pollution Degree	2
Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-540 °C
Ambient Air Temperature For Storage	-4085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.2 cm
Package 1 Width	8.6 cm
Package 1 Length	9.2 cm
Package 1 Weight	220 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	54
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	16.488 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations