Product datasheet

Main





Miniature circuit breaker (MCB), Acti9 C120N, 2P, 63A, B curve, 10000A (IEC/EN 60898-1), 10kA (IEC/EN 60947-2)

A9N18344

! Discontinued on: 30-Jun-2023

Range Of Product	C120	
Range	Acti9	
Product Name	C120	
Product Or Component Type	Miniature circuit-breaker	
Device Short Name	C120N	
Device Application	Distribution	
Poles Description	2P	
Number Of Protected Poles	2	
Neutral Position	Left	
[In] Rated Current	63 A at 30 °C	
Network Type	AC	
Trip Unit Technology	Thermal-magnetic	
Curve Code	В	
Breaking Capacity	lking Capacity 10000 A Icn at 230400 V AC 50/60 Hz conforming to EN/IEC 60898-1 6 kA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 10 kA Icu at <= 250 V DC conforming to EN/IEC 60947-2 20 kA Icu at 220240 V AC 50/60 Hz conforming to EN/IEC 60947-2 10 kA Icu at 380415 V AC 50/60 Hz conforming to EN/IEC 60947-2	
Suitability For Isolation	Yes conforming to IEC 60947-2	

Complementary

Network Frequency	50/60 Hz	
[Ue] Rated Operational Voltage	380415 V AC 50/60 Hz 220240 V AC 50/60 Hz 440 V AC 50/60 Hz <= 250 V DC 230400 V AC 50/60 Hz	
Magnetic Tripping Limit	35 x ln	
[Ics] Rated Service Breaking Capacity	7500 A 75 % conforming to EN/IEC 60898-1 - 230400 V AC 50/60 Hz 4.5 kA 75 % conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz 7.5 kA 75 % conforming to EN/IEC 60947-2 - 380415 V AC 50/60 Hz 15 kA 75 % conforming to EN/IEC 60947-2 - 220240 V AC 50/60 Hz 10 kA 100 % conforming to EN/IEC 60947-2 - <= 250 V DC	
Limitation Class	1 conforming to EN/IEC 60947-2	
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz conforming to EN/IEC 60947-2	

[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to EN/IEC 60947-2	
Contact Position Indicator	Yes	
Control Type	Toggle	
Local Signalling	ON/OFF indication	
Mounting Mode	Clip-on	
Mounting Support	35 mm symmetrical DIN rail	
Comb Busbar And Distribution Block Compatibility	YES	
9 Mm Pitches	6	
Height	81 mm	
Depth	73 mm	
Width	54 mm	
Net Weight	0.41 kg	
Colour	White	
Mechanical Durability	20000 cycles	
Electrical Durability	10000 cycles conforming to IEC 60947-2	
Connections - Terminals	Tunnel type terminals150 mm² rigid Tunnel type terminals1.535 mm² flexible	
Wire Stripping Length	15 mm	
Tightening Torque	3.5 N.m	
Earth-Leakage Protection	Separate block	

Environment

Standards	EN/IEC 60947-2 EN/IEC 60898-1	
Product Certifications	EAC	
Ip Degree Of Protection	IP20 conforming to IEC 60529	
Pollution Degree	3 conforming to IEC 60947-2	
Overvoltage Category	IV	
Tropicalisation	2 conforming to IEC 60068-1	
Relative Humidity	95 % at 55 °C	
Operating Altitude	2000 m	
Ambient Air Temperature For Operation	-2570 °C	
Ambient Air Temperature For Storage	-4085 °C	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.3 cm
Package 1 Width	6.8 cm
Package 1 Length	8.4 cm
Package 1 Weight	376 g
Unit Type Of Package 2	BB1

Number Of Units In Package 2	6
Package 2 Height	8.6 cm
Package 2 Width	9.6 cm
Package 2 Length	33.4 cm
Package 2 Weight	2.326 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	36
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	14.396 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations