Product datasheet

Specifications





MAN-STARTER SHORT CIR CONTACT 575VAC 1

GVAM11

Main

Range	TeSys
0	•
	TeSys Deca
Device Short Name	GVAM
Product Or Component Type	Auxiliary contact block
Product Compatibility	GV2L
	GV2ME
	GV2RT
	GV3L
	GV2P
	GV3P
	GV2LE
Range Compatibility	TeSys
	TeSys GV3 GV3P circuit breaker
	TeSys GV3 GV3L circuit breaker
Mounting Location	Left side
Auxiliary Contacts Operation	Short-circuit signal 1 C/O
Pole Contact Composition	1 C/O

Complementary

· · · · · · · · · · · · · · · · · ·		
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947-1 300 V conforming to UL 508 300 V conforming to CSA C22.2 No 14	
[Ue] Rated Operational Voltage	24240 V AC 2460 V DC	
[Ith] Conventional Free Air Thermal Current	2.5 A for fault signalling	
Mechanical Durability	100000 cycles	
Minimum Switching Current	5 mA	
Minimum Switching Voltage	17 V	
Protection Type	GB2CB circuit breaker GG fuse 10 A	
Rated Operational Power In Va	36 VA at 24 V AC-14 - electrical durability: 1000 cycles at 1.5 A 48 VA at 48 V AC-14 - electrical durability: 1000 cycles at 1 A 72 VA at 110127 V AC-14 - electrical durability: 1000 cycles at 0.5 A 72 VA at 230240 V AC-14 - electrical durability: 1000 cycles at 0.3 A	
Rated Operational Power In W	120 W at 240 V DC-13 - electrical durability: 100000 cycles 140 W at 110 V DC-13 - electrical durability: 100000 cycles 140 W at 24 V DC-13 - electrical durability: 100000 cycles 180 W at 60 V DC-13 - electrical durability: 100000 cycles 240 W at 48 V DC-13 - electrical durability: 100000 cycles 15 W at 48 V DC-13 - electrical durability: 1000 cycles 24 W at 24 V DC-13 - electrical durability: 1000 cycles 9 W at 60 V DC-13 - electrical durability: 1000 cycles	

Tightening Torque	1.4 N.m - on screw clamp terminals	
Height	89 mm	
Width	9.3 mm	
Depth	66 mm	
Net Weight	0.055 kg	
Colour	Dark grey	

Environment

Environmental Characteristic	Normal environment
Product Certifications	UKCA

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	7.0 cm
Package 1 Length	9.0 cm
Package 1 Weight	39 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	10.0 cm
Package 2 Width	10.5 cm
Package 2 Length	15.3 cm
Package 2 Weight	440 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	60
Package 3 Height	15 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	2.944 kg

Contractual warranty

Warranty

12 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Product datasheet

Connections and Schema

Short-Circuit Signalling Contacts GVAM11

