

# Product datasheet

Specifications



## miniature circuit breaker - xC60 - 3 poles - 16 A - C curve

A9N3P16C

### Main

Device application	Distribution
Range of product	Acti9
Range	Acti9
Product name	XC60
Product or component type	Miniature circuit-breaker
Device short name	xC60
Poles description	3P
Number of protected poles	3
[In] rated current	16 A
Network type	DC AC
Trip unit technology	Thermal-magnetic
Curve code	C
Utilisation category	Category A conforming to EN/IEC 60947-2
Suitability for isolation	Yes conforming to EN/IEC 60947-2

### Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	240 V AC 50/60 Hz 380...415 V AC 50/60 Hz 100...125 V DC
Magnetic tripping limit	8 x In +/- 20 %
Breaking capacity	10000 A Icn at 240 V AC 50/60 Hz conforming to EN/IEC 60898-1 10000 A Icn at 415 V AC 50/60 Hz conforming to EN/IEC 60898-1 15 kA Icu at 380...415 V AC 50/60 Hz conforming to EN/IEC 60947-2 15 kA Icu at 100...125 V DC conforming to EN/IEC 60947-2
[Ics] rated service breaking capacity	7.5 kA conforming to EN/IEC 60947-2 - 380...415 V AC 50/60 Hz 15 kA conforming to EN/IEC 60947-2 - 100...125 V DC
Limitation class	3 conforming to EN/IEC 60898-1 3 conforming to EN/IEC 60947-2
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to EN/IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-2
Contact position indicator	Yes

<b>Control type</b>	Toggle
<b>Local signalling</b>	ON/OFF indication
<b>Mounting mode</b>	Clip-on
<b>Mounting support</b>	35 mm DIN rail
<b>Comb busbar and distribution block compatibility</b>	Top: YES
<b>9 mm pitches</b>	6
<b>Height</b>	85 mm
<b>Width</b>	54 mm
<b>Depth</b>	77.5 mm
<b>Net weight</b>	0.31 kg
<b>Colour</b>	White
<b>Mechanical durability</b>	20000 cycles
<b>Electrical durability</b>	20000 cycles
<b>Connections - terminals</b>	Tunnel type terminals (bottom) 16 mm <sup>2</sup> flexible Tunnel type terminals (bottom) 25 mm <sup>2</sup> rigid Biconnect (top)
<b>Wire stripping length</b>	13 mm for top or bottom connection
<b>Tightening torque</b>	2 N.m
<b>Earth-leakage protection</b>	Separate block
<b>Product compatibility</b>	C60 auxiliary C60 accessories

## Environment

<b>Standards</b>	EN/IEC 60947-2 EN/IEC 60898-1
<b>IP degree of protection</b>	IP20 conforming to IEC 60529
<b>Pollution degree</b>	3
<b>Tropicalisation</b>	2 conforming to IEC 60068-1
<b>Relative humidity</b>	95 % at 55 °C
<b>Ambient air temperature for operation</b>	-30...70 °C
<b>Ambient air temperature for storage</b>	-40...85 °C

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	8.0 cm
<b>Package 1 Width</b>	5.0 cm
<b>Package 1 Length</b>	8.0 cm
<b>Package 1 Weight</b>	334.0 g

## Offer Sustainability

<b>Sustainable offer status</b>	Green Premium product
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>EU RoHS Directive</b>	Compliant <a href="#">EU RoHS Declaration</a>

---

<b>Mercury free</b>	Yes
<b>RoHS exemption information</b>	<a href="#">Yes</a>
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>
<b>Halogen content performance</b>	Halogen free plastic parts & cables product

---

### Recommended replacement(s)