Product datasheet

Specifications





TeSys LC1D.K capacitor duty contactor - 3P - 20 kVAR - 415 V -230 V AC coil

LC1DLKP7

Main

Range	TeSys TeSys Deca
Product Name	TeSys LC1D.K TeSys Deca
Product Or Component Type	Capacitor duty contactor
Device Short Name	LC1DLK
Device Application	Control
Contactor Application	Power factor correction
Utilisation Category	AC-6b
Poles Description	3P
Power Pole Contact Composition	3 NO
Device Location In System	Inside delta interruption Line interruption
[Ue] Rated Operational Voltage	Power circuit: 690 V AC 50/60 Hz
Reactive Power Rating	11 kvar at 230 V AC 50 Hz 60 °C 20 kvar at 400 V AC 50 Hz 60 °C 21 kvar at 440 V AC 50 Hz 60 °C 33 kvar at 690 V AC 50 Hz 60 °C
Control Circuit Type	AC at 50/60 Hz
[Uc] Control Circuit Voltage	230 V AC 50/60 Hz
Auxiliary Contact Composition	1 NO + 2 NC instantaneous
Electrical Durability	300000 cycles at Ue 400 V 200000 cycles at Ue 690 V
Mounting Support	DIN rail Plate
Standards	EN/IEC 60947-1 EN/IEC 60947-4-1 IEC 60335-1
Product Certifications	IECEE CB Scheme UKCA

Connections - Terminals	Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: solid
	Control circuit: screw clamp terminals 2 14 mm ² - cable stiffness: solid
	Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: flexible without cable end
	Control circuit: screw clamp terminals 2 14 mm ² - cable stiffness: flexible without cable end
	Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: flexible with cab end
	Control circuit: screw clamp terminals 2 12.5 mm ² - cable stiffness: flexible with cable end
	Power circuit: screw clamp terminals 1 2.516 mm ² - cable stiffness: solid
	Power circuit: screw clamp terminals 2 2.56 mm ² - cable stiffness: solid
	Power circuit: screw clamp terminals 1 1.510 mm ² - cable stiffness: flexible without cable end
	Power circuit: screw clamp terminals 2 1.56 mm ² - cable stiffness: flexible without cable end
	Power circuit: screw clamp terminals 1 110 mm ² - cable stiffness: flexible with cable end
	Power circuit: screw clamp terminals 2 14 mm ² - cable stiffness: flexible with cable end
Tightening Torque	Control circuit: 1.7 N.m - on screw clamp terminals Power circuit: 2.5 N.m - on screw clamp terminals
Maximum Operating Rate	240 cyc/h

Complementary

Auxiliary Contacts Type

type mechanically linked 1 NO + 2 NC conforming to IEC 60947-5-1

Environment

Ip Degree Of Protection	IP20 front face conforming to IEC 60529
Ambient Air Temperature For Operation	-560 °C
Ambient Air Temperature For Storage	-6080 °C
Operating Altitude	03000 m
Height	125 mm
Width	45 mm
Depth	127 mm
Net Weight	0.6 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.700 cm
Package 1 Width	19.400 cm
Package 1 Length	22.700 cm
Package 1 Weight	610.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	6
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.167 kg
Unit Type Of Package 3	P06

Number Of Units In Package 3	48
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	43.484 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations