

Product datasheet

Specifications



circuit breaker ComPact NSX250
DC PV, 250 A, 1000 V, TM-D trip
unit, 4 poles

LV438451

! To be discontinued

! Discontinued on: 30 Sept 2022

! End-of-service on: 30 Jun 2023

Main

Range	ComPact
Product Name	ComPact NSX DC
Range Of Product	ComPact NSX100...250 DC PV
Device Short Name	NSX250 DC PV
Product Or Component Type	Circuit breaker
Device Application	Distribution
Number Of Poles	4P
Protected Poles Description	4t
Neutral Position	Left
[In] Rated Current	250 A at 40 °C
[Ue] Rated Operational Voltage	1000 V DC
Network Type	DC
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	10 kA Icu at 1000 V DC conforming to IEC 60947-2
Trip Unit Name	TM-DC
Trip Unit Technology	Thermal-magnetic
Trip Unit Protection Functions	LI
Control Type	Toggle
Circuit Breaker Mounting Mode	Fixed

Complementary

[Ui] Rated Insulation Voltage	1000 V DC conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
[Ics] Rated Service Short-Circuit Breaking Capacity	5 kA at 1000 V DC conforming to IEC 60947-2
Mechanical Durability	5000 cycles
Electrical Durability	1000 cycles at 1000 V In
Mounting Support	Backplate
Upside Connection	Front

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Downside Connection	Front Rear
Connection Pitch	45 mm
Protection Type	L : for overload protection (thermal) I : for short-circuit protection (magnetic)
Trip Unit Rating	250 A at 40 °C
Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable
[Ir] Long-Time Protection Pick-Up Adjustment Range	0.7...1 x In
Earth-Leakage Protection	Without
Width (W)	185 mm
Height (H)	255 mm
Depth (D)	110 mm
Net Weight	7.9 kg

Environment

Standards	EN/IEC 60947
Product Certifications	CCC EAC Marine
Overvoltage Category	Class II
Electrical Shock Protection Class	Class II
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C
Relative Humidity	0...95 %
Operating Altitude	0...2000 m without derating 2000 m...5000 m with derating

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30.0 cm
Package 1 Width	30.0 cm
Package 1 Length	40.0 cm
Package 1 Weight	10.0 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	11
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	110.766 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration	Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	End of Life Information	