



DOL combination starter - TeSys GV2-ME - 1...1.6 A - 220...230 V AC

GV2ME06K1M7

Discontinued on: 31-Mar-2021

! End-of-service on: 03-Nov-2020

① Discontinued

Main

Range	TeSys
Device Short Name	GV2ME
Product Or Component Type	Motor starter
Motor Starter Type	Non reversing
Poles Description	3P
Utilisation Category	AC-3
Motor Power Kw	0.37 kW at 400/415 V AC 50/60 Hz 0.55 kW at 400/415 V AC 50/60 Hz 0.37 kW at 440 V AC 50/60 Hz 0.55 kW at 440 V AC 50/60 Hz 0.37 kW at 500 V AC 50/60 Hz 0.55 kW at 500 V AC 50/60 Hz 0.55 kW at 500 V AC 50/60 Hz 0.75 kW at 500 V AC 50/60 Hz
[Uc] Control Circuit Voltage	220/230 V AC 50/60 Hz
Magnetic Tripping Current	22.5 A

Complementary

Device Composition	combination block GV2AF01 3-pole contactor motor circuit breaker type GV2ME	
Coordination Type	Type 1	
Thermal Protection Adjustment Range	11.6 A	
Breaking Capacity	50 kA lq at 400/415 V AC 50/60 Hz conforming to IEC 60947-4-1 50 kA lq at 440 V AC 50/60 Hz conforming to IEC 60947-4-1 50 kA lq at 500 V AC 50/60 Hz conforming to IEC 60947-4-1	
Net Weight	0.46 kg	
Height	152 mm	
Width	45 mm	
Depth	87 mm	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	8.5 cm

Package 1 Length	15.8 cm
Package 1 Weight	493 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins