Product datasheet

Specifications





TeSys VARIO - Switch body for switch-disconnector - 3 poles - 80 A

V4

Main

Walli	
Range	TeSys
Product Name	TeSys VARIO
Device Short Name	V
Product Type	Switch body
Complementary	
Mounting Support	Plate Symmetrical rail
Performance Level	High performance
Number Of Poles	3P
Contact Type And Composition	3 NO
Network Type	DC AC
Network Frequency	50/60 Hz
[Ue] lec Rated Operational Voltage	690 V AC 50/60 Hz
lec Rated Operational Power In W	15 kW at 230240 V (AC-3) 22 kW at 400415 V (AC-3) 30 kW at 500 V (AC-3) 30 kW at 690 V (AC-23A) 37 kW at 500 V (AC-23A) 18.5 kW at 690 V (AC-3) 18.5 kW at 230240 V (AC-23A) 30 kW at 400415 V (AC-23A)
[Ie] Rated Operational Current	57 A AC-23 Ue: 400 V
[Ith] Conventional Free Air Thermal Current	80 A
[Ithe] Conventional Enclosed Thermal Current	63 A
Making Capacity (I Rms)	800 A at 400 V AC-21A 800 A at 400 V AC-22A 800 A at 400 V AC-23A
Breaking Capacity	640 A at 400 V (AC-21A) 640 A at 400 V (AC-22A) 640 A at 400 V (AC-23A)

Dicaking Capacity	040 A at 400 V (AC-2 TA)	
	640 A at 400 V (AC-22A)	
	640 A at 400 V (AC-23A)	
Rated Conditional Short Circuit	10 kA at 400 V - associated fuse 80 A aM	
Current	10 kA at 400 V - associated fuse 80 A gG	
[Icm] Rated Short Circuit Making Capacity	2.1 kA at 400 V at Ipeak	
Intermittent Duty Class	30	
Suitability For Isolation	Yes	

[Uimp] Rated Impulse Withstand	8 kV
Voltage	
[Icw] Rated Short-Time Withstand Rms Current	960 A at 400 V duration: 1 s
Mechanical Durability	30000 cycles
Electrical Durability	30000 cycles AC-21 30000 cycles DC-15
lec Terminal Connection	Power circuit: screw clamp terminals16 mm ² - flexible - with cable end Power circuit: screw clamp terminals25 mm ² - solid
Tightening Torque	Power circuit: 4 N.m - on screw clamp terminals
Height	83 mm
Width	60 mm
Depth	65 mm
Product Weight	0.5 kg

Environment

Standards	IEC 60947-3	
Product Certifications	UL	
	CSA	
	GL	
	UKCA	
Degree Of Protection	IP20 conforming to IEC 60529	
Protective Treatment	TC	
Mechanical Robustness	Vibrations 10150 Hz (1 gn) conforming to IEC 60068-2-6 Shocks 11 ms (30 Gn) conforming to IEC 60068-2-27	
Ambient Air Temperature For Operation	-2050 °C	
Fire Resistance	960 °C conforming to IEC 60695-2-1	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.000 cm
Package 1 Width	8.500 cm
Package 1 Length	8.000 cm
Package 1 Weight	297.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	12
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.906 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	192
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm

Package 3 Weight

Contractual warranty

Warranty

12 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations