Product datasheet





IIoT Edge Box Core eMMC DC Linux TPM

HMIBSCEA53D1L0T

Main

Range Of Product	Harmony iPC	
Product Or Component Type	IIoT Edge Box Core	
Device Short Name	IIoT Edge Box Core	
Range Compatibility	HMIYMIN4GUS1 Interface Mini PCIe 4G US for iPC HMIYMIN4GEU1 Interface Mini PCIe 4G EU for iPC HMIYMIN8AI1 Interface Mini PCIe 8x Analog Input 0-10V HMIYBIN2AIM21 Interface M.2 2x Analog Input 0-10V/4-20mA	
Accessory / Separate Part Destination	Celullar 4G and analog Inputs	
Processor Name	ARM Cortex-A53 quad core 1.2 GHz Qualcomm Snapdragon 410	
Operating System	Linux Yocto (Linux Yocto project Krogoth 2.1) Linux Yocto (BitBake branch 1.30.0) Linux Yocto (Linux Kernel 4.4.38)	
Software Package	Node-RED and system nodes default IIoT Wiring	

Complementary

Mounting Location	Book mounting Flat mounting Wall mounting
Data Storage Equipment	8 GB eMMC (soldered)
Memory Description	1 GB RAM LPDDR3 internal (not expandable)
Free Slots	1 SD card SD 3.0, max raw transfer rate 104 MBps . Supports SD,SDHC,SDXC (Standard 32 mm x 24 mm)
Number Of Slots	1 slot(s) for mini PCI Express full-size with optional interface plate, 1 slot(s) for M.2 not for storage,
Number Of Slots Available For Expansion	1.0 slot(s) for mini PCle 1.0 slot(s) for M.2 (not for storage)
Display Resolution	1920 x 1080 pixels at 60 Hz
Watchdog Timer	1255 ms
Type Of Cooling	Fanless
Electrical Connection	Screw connector, connector type: pin, 1 way, circuit application: ground - location: bottom Connector, connector type: SMA - location: top
Integrated Connection Type	HDMI for For configuration only with 1 on bottom Ethernet with 2 RJ45 SMSC LAN7500, transmission rate: 10/100/1000 Mbps on bottom IEEE 1588 not supported COM1 serial link for battery backup with 1 male SUB-D 9 RS232/422/485 non-isolated USB 2.0 port with 2.0 USB type A, transmission rate: 480 Mbit/s on bottom TPM connector Ver 2.0 for cyber security - hardware encryption TPM module by

25-Apr-2024 Life Is On Schneider

default on motherboard



1.0 WCN3620 Wi-Fi 2.4 GHz conforming to IEEE 802.11 b/g/n	
1.0 WCN3620 Bluetooth 4.1	
Secure password boot	
1.0 GPIO Pin, 8 pins bottom(Software utility provided)	
24 V DC power supply	
100240 V AC power supply	
1224 V	
0.43 A	
16 W	
Resettable	
IIoT Edge Box Core	
46 mm	
150 mm	
157 mm	
1 kg	
	1.0 WCN3620 Bluetooth 4.1 Secure password boot 1.0 GPIO Pin, 8 pins bottom(Software utility provided) 24 V DC power supply 100240 V AC power supply 1224 V 0.43 A 16 W Resettable IloT Edge Box Core 46 mm 150 mm

Environment

Standards	Class A group 1 IEC 55011 IEC 61000-6-4 IEC 61131-2 FCC part 15 UL 60950
Product Certifications	CE CULus UL 60950 for IT equipments CCC RCM EAC RED FCC RF IC SRRC TELEC FAC ANATEL
Quality Labels	CE
Directives	2004/108/EC - electromagnetic compatibility 2006/95/EC - low voltage directive
Ip Degree Of Protection	IP40 conforming to IEC 60529
Electromagnetic Compatibility	Immunity to high frequency interference conforming to IEC 61000-4 Disturbing field emission class A conforming to IEC 55011 Conducted and radiated emissions class A conforming to EN 55022
Ambient Air Temperature For Storage	-2060 °C conforming to IEC 60068-2-2 -2060 °C conforming to IEC 60068-2-14
Relative Humidity	1095 % non-condensing conforming to IEC 60068-2-30
Ambient Air Temperature For Operation	050 °C (by default) conforming to IEC 60068-2-2 050 °C flat mounting 045 °C on mini PCle 045 °C flat mounting on mini PCle
Operating Altitude	2000 m conforming to IEC 60664-1
Vibration Resistance	2 gn (f = 5500 Hz) eMMC

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	22.0 cm
Package 1 Length	32.0 cm
Package 1 Weight	1.362 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	6
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	8.942 kg

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

HMIBSCEA53D1L0T


Dimensions Drawings

Dimensions



Mounting and Clearance

Spacing Requirements



- 1: Air out
- 2: Air in
- (1) Book mounting: Vertical mounting with rear fixing
- (2) Wall mounting: Vertical mounting with side fixing
- (3) Horizontal mounting