



TeSys Deca contactor , 4P(4 NO) , AC-1 , <= 440V, 200A , 415V AC 50 Hz coil

LC1D115004N5

! End-of-service on: 04-Nov-2020

(!) Discontinued

Main

Range	TeSys	
Range Of Product	TeSys Deca	
Product Or Component Type	Contactor	
Device Short Name	LC1D	
Contactor Application	Resistive load	
Utilisation Category	AC-1 AC-3 AC-3e AC-4	
Poles Description	4P	
[Ue] Rated Operational Voltage	Power circuit: <= 1000 V AC 25400 Hz Power circuit: <= 460 V DC	
[le] Rated Operational Current	perational Current 200 A (at <60 °C) at <= 440 V AC AC-1 for power circuit	
[Uc] Control Circuit Voltage	ntrol Circuit Voltage 415 V AC 50 Hz	

Complementary

LC1D

Compatibility Code

	20.5
Pole Contact Composition	4 NO
Contact Compatibility	M14
Protective Cover	With
[Ith] Conventional Free Air Thermal Current	200 A (at 60 °C) for power circuit
Irms Rated Making Capacity	1260 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	1100 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	250 A 40 °C - 10 min for power circuit 550 A 40 °C - 1 min for power circuit 950 A 40 °C - 10 s for power circuit 1100 A 40 °C - 1 s for power circuit
Associated Fuse Rating	250 A gG at <= 690 V coordination type 1 for power circuit 200 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	0.6 mOhm - Ith 200 A 50 Hz for power circuit
Power Dissipation Per Pole 24 W AC-1	
[Ui] Rated Insulation Voltage	Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Power circuit: 1000 V conforming to IEC 60947-4-1
Overvoltage Category	III

Pollution Degree	3	
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947	
Safety Reliability Level	B10d = 684932 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 10000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1	
Mechanical Durability	8 Mcycles	
Electrical Durability	0.8 Mcycles 200 A AC-1 at Ue <= 440 V	
Control Circuit Type	AC at 50 Hz	
Coil Technology	Without built-in suppressor module	
Control Circuit Voltage Limits	0.30.6 Uc (-4070 °C):drop-out AC 50 Hz 0.851.1 Uc (-4055 °C):operational AC 50 Hz 11.1 Uc (5570 °C):operational AC 50 Hz	
Inrush Power In Va	300 VA 50 Hz cos phi 0.8 (at 20 °C)	
Hold-In Power Consumption In Va	22 VA 50 Hz cos phi 0.3 (at 20 °C)	
Heat Dissipation	38 W at 50 Hz	
Operating Time	620 ms opening 2050 ms closing	
Maximum Operating Rate	2400 cyc/h 60 °C	
Tightening Torque	Control circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 12.5 mm² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 12.5 mm² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 12.5 mm² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: solid without cable end Power circuit: connector 1 10120 mm² - cable stiffness: flexible without cable end Power circuit: connector 2 1050 mm² - cable stiffness: flexible with cable end Power circuit: connector 2 1050 mm² - cable stiffness: flexible with cable end Power circuit: connector 1 10120 mm² - cable stiffness: solid without cable end Power circuit: connector 2 1050 mm² - cable stiffness: solid without cable end Power circuit: connector 2 1050 mm² - cable stiffness: solid without cable end Power circuit: connector 2 1050 mm² - cable stiffness: solid without cable end	
Tightening Torque	Control circuit: 1.2 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.2 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 12 N.m - on connector hexagonal screw head 4 mm	
Mounting Support Environment	Plate Rail	
	004.000.014.44	
Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508	
Product Certifications Ip Degree Of Protection	UL CSA GOST BV GL LROS (Lloyds register of shipping) DNV CCC RINA IP20 front face conforming to IEC 60529	

Protective Treatment TH conforming to IEC 60068-2-30		
Climatic Withstand	conforming to IACS E10 exposure to damp heat conforming to IEC 60947-1 Annex Q category D exposure to damp heat	
Permissible Ambient Air Temperature Around The Device	-4060 °C 6070 °C with derating	
Operating Altitude	03000 m	
ire Resistance 850 °C conforming to IEC 60695-2-1		
Flame Retardance	V1 conforming to UL 94	
Mechanical Robustness Vibrations contactor open (2 Gn, 5300 Hz) Vibrations contactor closed (4 Gn, 5300 Hz) Shocks contactor closed (15 Gn for 11 ms) Shocks contactor open (6 Gn for 11 ms)		
Height	158 mm	
Width	150 mm	
Depth	132 mm	
Net Weight	2.86 kg	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Pvc Free	

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

11-May-2024