

Product datasheet

Specifications



Actassi CL-MNC patch cord, F/UTP, 4P, category 5e, 155 MHz, LSZH, 1 m, grey

VDIP184546010

Main

Range	Actassi
Product	Patch cord
Colour	Patchcord: grey
Quantity Per Set	1
Cable Shielding Type	F/UTP
Provided Component	Grey coloured clips Green coloured clips Red coloured clips

Complementary

Product Compatibility	Coloured clips red Coloured clips green Coloured clips yellow Coloured clips blue
Length (Customizable Value In Configurator)	0...1 m
Communication Network Type	10GBASE-T
Connector Type	RJ45
Communication Network Category	5e
Transmission Frequency	155 MHz
Awg Gauge	AWG 26
Input Impedance	100 Ohm
Material	Solid bare copper: conductor PE (polyethylene): wire insulation
Targeted Region	Europe

Environment

Ambient Air Temperature For Installation	0...50 °C
Ambient Air Temperature For Operation	-20...60 °C
Ambient Air Temperature For Storage	-20...60 °C
Temperature Resistance	60 °C
Flame Retardance	LSZH
Product Certifications	Delta

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EIA/TIA-568-C.2 ISO/IEC 11801:2011 Ed.2.2 EN 50173 Ed.3 IEC 61935-2
-----------	--

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.2 cm
Package 1 Width	20.5 cm
Package 1 Length	25 cm
Package 1 Weight	47 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
Circularity Profile	No need of specific recycling operations