



empty control station - XAP-A - plastic - 4 openings in 2 columns

XAPA1104

Main

Range Of Product	Harmony XAP				
Product Or Component Type	Empty control station without hinges				
Device Short Name	XAPA				
Product Destination	For Ø 22 mm control and signalling units				
Product Front Plate Size	85 x 146 mm				
Usable Depth 83 mm					
Number Of Cut-Out	4 cut-outs				
Colour Of Base Of Enclosure Grey					
Colour Of Cover	Grey				
Material	Glass reinforced polyester				
Cable Entry	Undrilled				
Device Mounting	Flush				
Ip Degree Of Protection	IP65 conforming to IEC 60529 IP69 conforming to NF C 20-010 IP69K				
Resistance To Chemical Agents	High resistant to acids High resistant to all solvents High resistant to bases High resistant to diesel High resistant to mineral salts High resistant to oils and greases High resistant to petrol High resistant to sea water				

Complementary

Number Of Vertical Rows	2		
Flame Retardance	M3 conforming to CSTB VO conforming to UL 94		
Net Weight	0.47 kg		

Environment

Protective Treatment	TH TC
Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-4070 °C
Overvoltage Category	Class II conforming to IEC 60536

Class II conforming to NF C 20-030

Fire Resistance	850 °C conforming to NF C 20-455	
	960 °C conforming to IEC 92	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.000 cm
Package 1 Width	9.000 cm
Package 1 Length	15.700 cm
Package 1 Weight	493.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	6.497 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	96
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	61.532 kg

Contractual warranty

Warranty 12 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


⊘	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
9	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Circularity Profile	No need of specific recycling operations		

Dimensions Drawings

Dimensions and Fixing




- (2) $2 \times \emptyset$ 5.6 mm/0.22 in. holes, depth 12 mm/0.47 in.
- P Usable depth

а		b		G		H .	
mm	in.	mm	in.	mm	in.	mm	in.
85	3.35	146	5.75	70	2.76	105	4.13

Refer to the product characteristics to get the number of cut-outs.

Cut-out interaxis dimensions (vertical mounting)



- b1 Vertical interaxis: 40 mm/1.57 in.
- b2 Horizontal interaxis: 30 mm/1.18 in.