Product datasheet

Specification





REVERSING CONTACTOR 575VAC 9A IEC

LC2D09M7

Main

Main					
Range	TeSys TeSys Deca				
Product Name	TeSys D TeSys Deca				
Product Or Component Type	Reversing contactor				
Device Short Name	LC2D				
Contactor Application	Motor control Resistive load				
Utilisation Category	AC-1 AC-3 AC-3e				
Device Presentation	Preassembled with reversing power busbar				
Poles Description	3P				
Power Pole Contact Composition	3 NO				
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC				
[le] Rated Operational Current	9 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 25 A (at <60 °C) at <= 440 V AC AC-1 for power circuit				
Motor Power Kw	2.2 kW at 220230 V AC 5060 Hz 4 kW at 380400 V AC 5060 Hz 4 kW at 415 V AC 5060 Hz 4 kW at 440 V AC 5060 Hz 5.5 kW at 500 V AC 5060 Hz 5.5 kW at 660690 V AC 5060 Hz				
Motor Power Hp (UI / Csa)	0.5 hp at 115 V AC 60 Hz for 1 phase motors 1 hp at 230/240 V AC 60 Hz for 1 phase motors 2 hp at 200/208 V AC 60 Hz for 3 phases motors 2 hp at 230/240 V AC 60 Hz for 3 phases motors 5 hp at 460/480 V AC 60 Hz for 3 phases motors 7.5 hp at 575/600 V AC 60 Hz for 3 phases motors				
Control Circuit Type	AC at 50/60 Hz				
[Uc] Control Circuit Voltage	220 V AC 50/60 Hz				
Auxiliary Contact Composition	1 NO + 1 NC				
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947				
Overvoltage Category	III				
[Ith] Conventional Free Air Thermal Current 10 A (at 60 °C) for signalling circuit 25 A (at 60 °C) for power circuit					
Irms Rated Making Capacity	250 A at 440 V for power circuit conforming to IEC 60947 140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1				
Rated Breaking Capacity	250 A at 440 V for power circuit conforming to IEC 60947				

[Icw] Rated Short-Time Withstand Current	30 A 40 °C - 10 min for power circuit 61 A 40 °C - 1 min for power circuit 105 A 40 °C - 10 s for power circuit 210 A 40 °C - 1 s for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit				
Associated Fuse Rating	25 A gG at <= 690 V coordination type 1 for power circuit 20 A gG at <= 690 V coordination type 2 for power circuit 10 A gG for signalling circuit conforming to IEC 60947-5-1				
Average Impedance	2.5 mOhm - Ith 25 A 50 Hz for power circuit				
[Ui] Rated Insulation Voltage	Power circuit: 690 V conforming to IEC 60947-4-1 Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified Signalling circuit: 600 V UL certified				
Electrical Durability	0.6 Mcycles 25 A AC-1 at Ue <= 440 V 2 Mcycles 9 A AC-3 at Ue <= 440 V 2 Mcycles 9 A AC-3e at Ue <= 440 V				
Power Dissipation Per Pole	0.2 W AC-3 1.56 W AC-1 0.2 W AC-3e				
Front Cover	With				
Interlocking Type	Mechanical				
Mounting Support	Plate Rail				
Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 IEC 60335-1				
Product Certifications	DNV CSA CCC UL GL LROS (Lloyds register of shipping) BV RINA GOST UKCA				
Connections - Terminals	Power circuit: screw clamp terminals 1 cable(s) 14 mm²flexible without cable end Power circuit: screw clamp terminals 2 cable(s) 14 mm²flexible without cable end Power circuit: screw clamp terminals 1 cable(s) 14 mm²flexible with cable end Power circuit: screw clamp terminals 2 cable(s) 125 mm²flexible with cable end Power circuit: screw clamp terminals 1 cable(s) 14 mm²solid Power circuit: screw clamp terminals 2 cable(s) 14 mm²solid Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 12.5 mm²flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm²solid Control circuit: screw clamp terminals 2 cable(s) 14 mm²solid				
Tightening Torque	Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2 Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver pozidriv No 2				
Operating Time	1222 ms closing 419 ms opening				

Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1				
Mechanical Durability	15 Mcycles				
Maximum Operating Rate	3600 cyc/h 60 °C				

Complementary

Coil Technology	Without built-in suppressor module 0.30.6 Uc (-4070 °C):drop-out AC 50/60 Hz 0.81.1 Uc (-4060 °C):operational AC 50 Hz 0.851.1 Uc (-4060 °C):operational AC 60 Hz 11.1 Uc (6070 °C):operational AC 50/60 Hz				
Control Circuit Voltage Limits					
Inrush Power In Va	70 VA 60 Hz cos phi 0.75 (at 20 °C) 70 VA 50 Hz cos phi 0.75 (at 20 °C)				
Hold-In Power Consumption In Va	7.5 VA 60 Hz cos phi 0.3 (at 20 °C) 7 VA 50 Hz cos phi 0.3 (at 20 °C)				
Heat Dissipation	23 W at 50/60 Hz				
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1				
Signalling Circuit Frequency	25400 Hz				
Minimum Switching Current	5 mA for signalling circuit				
Minimum Switching Voltage	17 V for signalling circuit				
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact				
nsulation Resistance > 10 MOhm for signalling circuit					

Environment

Ip Degree Of Protection	IP20 front face conforming to IEC 60529				
Climatic Withstand	conforming to IACS E10 conforming to IEC 60947-1 Annex Q category D				
Protective Treatment	TH conforming to IEC 60068-2-30				
Pollution Degree	3				
Ambient Air Temperature For Operation	emperature For -4060 °C 6070 °C with derating				
Ambient Air Temperature For Storage	-6080 °C				
Operating Altitude	03000 m				
Fire Resistance	850 °C conforming to IEC 60695-2-1				
Flame Retardance	V1 conforming to UL 94				
Mechanical Robustness	Vibrations contactor open: 2 Gn, 5300 Hz Vibrations contactor closed: 4 Gn, 5300 Hz Shocks contactor open: 10 Gn for 11 ms Shocks contactor closed: 15 Gn for 11 ms				
Height	77 mm				
Width 90 mm					
Depth	86 mm				
Net Weight	0.687 kg				

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.400 cm
Package 1 Width	9.500 cm
Package 1 Length	14.000 cm
Package 1 Weight	798.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	6
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.096 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	96
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	89.920 kg

Contractual warranty

Warranty 18 months

19-Apr-2024



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information Yes	
Ø	Pvc Free	


Certifications & Standards


Reach Regulation	REACh Declaration			
Eu Rohs Directive	Compliant EU RoHS Declaration			
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins			
Circularity Profile	End of Life Information			

LC2D09M7

Dimensions Drawings

Dimensions





LC2 or 2 x LC1	а	b	c ⁽¹⁾	e1	e2	G
D09 to D18 (AC)	90	77	86	4	1.5	80
D093 to D123 (AC)	90	99	86	_	_	80
D09 to D18 (DC)	90	77	95	4	1.5	80
D093 to D123 (DC)	90	99	95	_	_	80
D25 to D38 (AC)	90	85	92	9	5	80
D183 to D383 (AC)	90	99	92	_	_	80
D25 to D32 (DC)	90	85	101	9	5	80
D183 to D383 (DC)	90	99	101	_	_	80

e1 and e2: including cabling.

(1) With safety cover, without add-on block.

Connections and Schema

Wiring

