



# TeSys D reversing contactor - 3P(3 NO) - AC-3 - <= 440 V 38 A - 72 V DC coil

LC2D386SL

! End-of-service on: 04-Nov-2020

① Discontinued

### Main

Mani		
Range	TeSys	
Product Name	TeSys D	
Product Or Component Type	Reversing contactor	
Device Short Name	LC2D	
Contactor Application	Resistive load Motor control	
Utilisation Category	AC-3 AC-1	
Device Presentation	Preassembled with reversing power busbar	
Poles Description	3P	
Power Pole Contact Composition	3 NO	
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC	
[le] Rated Operational Current	50 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 38 A (at <60 °C) at <= 440 V AC AC-3 for power circuit	
Motor Power Kw	9 kW at 220230 V AC 50 Hz 18.5 kW at 380400 V AC 50 Hz 18.5 kW at 415440 V AC 50 Hz 18.5 kW at 500 V AC 50 Hz 18.5 kW at 660690 V AC 50 Hz	
Motor Power Hp (UI / Csa)	10 hp at 230/240 V AC 60 Hz for 3 phases motors 5 hp at 240 V AC 60 Hz for 1 phase motors 10 hp at 200/208 V AC 60 Hz for 3 phases motors 20 hp at 480 V AC 60 Hz for 3 phases motors 25 hp at 600 V AC 60 Hz for 3 phases motors	
Control Circuit Type	DC low consumption	
[Uc] Control Circuit Voltage	72 V DC	
Auxiliary Contact Composition	1 NO + 1 NC	
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947	
Overvoltage Category	III	
[lth] Conventional Free Air Thermal Current	10 A (at 60 °C) for signalling circuit 50 A (at 60 °C) for power circuit	
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 550 A at 440 V for power circuit conforming to IEC 60947	
Rated Breaking Capacity	550 A at 440 V for power circuit conforming to IEC 60947	

[Icw] Rated Short-Time Withstand Current	60 A 40 °C - 10 min for power circuit 430 A 40 °C - 1 s for power circuit 150 A 40 °C - 1 min for power circuit 310 A 40 °C - 10 s for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit	
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 63 A gG at <= 690 V coordination type 1 for power circuit 63 A gG at <= 690 V coordination type 2 for power circuit	
Average Impedance	2 mOhm - Ith 50 A 50 Hz for power circuit	
[Ui] Rated Insulation Voltage	Power circuit: 690 V conforming to IEC 60947-4-1 Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified Signalling circuit: 600 V UL certified	
Electrical Durability	1.4 Mcycles 50 A AC-1 at Ue <= 440 V 1.4 Mcycles 38 A AC-3 at Ue <= 440 V	
Power Dissipation Per Pole	5 W AC-1 3 W AC-3	
Front Cover	With	
Interlocking Type	Mechanical	
Mounting Support	Rail Plate	
Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508	
Product Certifications	GOST CCC CSA BV RINA GL UL LROS (Lloyds register of shipping) DNV	
Connections - Terminals	Control circuit: lugs-ring terminals (external diameter: 8 mm) Power circuit: lugs-ring terminals (external diameter: 10 mm)	
Tightening Torque	Control circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver flat Ø 6 mm M3.5 Control circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver Philips No 2 M3.5 Power circuit: 2.5 N.m - on lugs-ring terminals - with screwdriver flat Ø 8 mm M4 Power circuit: 2.5 N.m - on lugs-ring terminals - with screwdriver Philips No 2 M4	
Operating Time	65.4588.55 ms closing 2030 ms opening	
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1	
Mechanical Durability	30 Mcycles	
Maximum Operating Rate	3600 cyc/h 60 °C	
Complementary  Coil Technology	Built-in bidirectional peak limiting diode suppressor	
Control Circuit Voltage Limits	0.10.3 Uc (-4070 °C):drop-out DC 0.81.25 Uc (-4060 °C):operational DC 11.25 Uc (6070 °C):operational DC	
Time Constant	40 ms	

Inrush Power In W	2.4 W (at 20 °C)	
Hold-In Power Consumption In W	2.4 W at 20 °C	
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1	
Signalling Circuit Frequency	25400 Hz	
Minimum Switching Current	5 mA for signalling circuit	
Minimum Switching Voltage	17 V for signalling circuit	
Non-Overlap Time	Time 1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact	
Insulation Resistance	> 10 MOhm for signalling circuit	

## **Environment**

Ip Degree Of Protection	IP20 front face conforming to IEC 60529	
Protective Treatment	TH conforming to IEC 60068-2-30	
Pollution Degree	3	
Ambient Air Temperature For Operation	-4060 °C 6070 °C with derating	
Ambient Air Temperature For Storage	-6080 °C	
Operating Altitude	03000 m	
Fire Resistance	850 °C conforming to IEC 60695-2-1	
Flame Retardance	V1 conforming to UL 94	
Mechanical Robustness	Vibrations contactor open: 2 Gn, 5300 Hz Vibrations contactor closed: 4 Gn, 5300 Hz Shocks contactor closed: 15 Gn for 11 ms Shocks contactor open: 8 Gn for 11 ms	
Height	85 mm	
Width	90 mm	
Depth	101 mm	
Net Weight	1.137 kg	

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information Y	res
<b>Ø</b>	Pvc Free	

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information