# **Product datasheet**

Specifications

|--|



## 4 THREADED BARS 160A L1400/ LINERGY BS BB

04171

() Discontinued on: 18-Nov-2021

(!) End-of-service on: 30-Jun-2022

(!) Discontinued

#### Main

Range	Linergy
Range Of Product	Linergy
Product Or Component Type	Copper busbar
Product Name	Linergy BS
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P enclosure
Busbar Description	Flat bar
Quantity Per Set	Set of 4

#### Complementary

Installation Direction	Vertical, operating position: rear
Installation Description	Cubicle - width 650 mm Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Floor-standing duct - width 300 mm
	Wall-mounted duct - width 300 mm
[Ui] Rated Insulation Voltage	1000 V
[le] Rated Operational Current	160 A
[Ipk] Rated Peak Withstand Current	30 kA
I <sup>2</sup> T On Activation	100000 kA².s
Busbar Cross Section	15 x 5 mm
Length	1400 mm
Net Weight	3.74 kg
Type Of Busbar Connection	M6 threaded hole
Connection Pitch	Connection each 25 mm
Support Thickness	5 mm

#### Environment

Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA

#### **Packing Units**

Unit Type Of Package 1

PCE

Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	13 cm
Package 1 Length	150 cm
Package 1 Weight	3.74 kg

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins