# **Product datasheet**

Specification





# Reversing Contactor, TeSys Deca, 3P(3NO), AC-3, <= 440V 40A, 115V AC 50/60 Hz coil

LC2D40AFE7

#### Main

| Mani   |   |
|--|---|
| Range  | TeSys<br>TeSys Deca   |
| Product Name                                   | TeSys Deca  |
| Product Or Component Type                      | Reversing contactor   |
| Device Short Name                              | LC2D  |
| Contactor Application                          | Motor control<br>Resistive load   |
| Utilisation Category                           | AC-1<br>AC-3<br>AC-3e   |
| Device Presentation                            | Preassembled with reversing power busbar  |
| Poles Description                              | 3P  |
| Power Pole Contact Composition                 | 3 NO  |
| [Ue] Rated Operational Voltage                 | Power circuit: <= 690 V AC 25400 Hz<br>Power circuit: <= 300 V DC   |
| [le] Rated Operational Current                 | 40 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 60 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 40 A (at <60 °C) at <= 440 V AC AC-3e for power circuit   |
| Motor Power Kw                                 | 11 kW at 220230 V AC 5060 Hz<br>18.5 kW at 380400 V AC 5060 Hz<br>22 kW at 415 V AC 5060 Hz<br>22 kW at 440 V AC 5060 Hz<br>22 kW at 500 V AC 5060 Hz<br>30 kW at 660690 V AC 5060 Hz   |
| Motor Power Hp (UI / Csa)                      | 5 hp at 230/240 V AC 60 Hz for 1 phase motors 10 hp at 230/240 V AC 60 Hz for 3 phases motors 30 hp at 575/600 V AC 60 Hz for 3 phases motors 10 hp at 200/208 V AC 60 Hz for 3 phases motors 3 hp at 115 V AC 60 Hz for 1 phase motors 30 hp at 460/480 V AC 60 Hz for 3 phases motors |
| Control Circuit Type                           | AC at 50/60 Hz  |
| [Uc] Control Circuit Voltage                   | 115 V AC 50/60 Hz   |
| Auxiliary Contact Composition                  | 1 NO + 1 NC   |
| [Uimp] Rated Impulse Withstand Voltage         | 6 kV conforming to IEC 60947  |
| Overvoltage Category                           | III   |
| [Ith] Conventional Free Air<br>Thermal Current | 10 A (at 60 °C) for signalling circuit<br>60 A (at 60 °C) for power circuit   |
| Irms Rated Making Capacity                     | 140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 800 A at 440 V for power circuit conforming to IEC 60947  |
| Rated Breaking Capacity                        | 800 A at 440 V for power circuit conforming to IEC 60947  |

| [Icw] Rated Short-Time Withstand Current | 72 A 40 °C - 10 min for power circuit 165 A 40 °C - 1 min for power circuit 320 A 40 °C - 10 s for power circuit 720 A 40 °C - 1 s for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit  |
|--|--|
| Associated Fuse Rating                   | 10 A gG for signalling circuit conforming to IEC 60947-5-1 80 A gG at <= 690 V coordination type 1 for power circuit 80 A gG at <= 690 V coordination type 2 for power circuit   |
| Average Impedance                        | 1.5 mOhm - Ith 60 A 50 Hz for power circuit  |
| [Ui] Rated Insulation Voltage            | Power circuit: 690 V conforming to IEC 60947-4-1 Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified Signalling circuit: 600 V UL certified   |
| Electrical Durability                    | 1.5 Mcycles 40 A AC-3 at Ue <= 440 V<br>1.4 Mcycles 60 A AC-1 at Ue <= 440 V<br>1.5 Mcycles 40 A AC-3e at Ue <= 440 V  |
| Power Dissipation Per Pole               | 2.4 W AC-3<br>5.4 W AC-1<br>2.4 W AC-3e  |
| Front Cover                              | With   |
| Interlocking Type                        | Mechanical   |
| Mounting Support                         | Rail<br>Plate  |
| Standards                                | CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 IEC 60335-1   |
| Product Certifications                   | UL CSA RINA GOST CCC DNV LROS (Lloyds register of shipping) GL BV UKCA   |
| Connections - Terminals                  | Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 12.5 mm²flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm²solid Control circuit: screw clamp terminals 2 cable(s) 14 mm²solid Power circuit: EverLink BTR screw connectors 1 cable(s) 135 mm²flexible without cable end Power circuit: EverLink BTR screw connectors 2 cable(s) 125 mm²flexible without cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 135 mm²flexible with cable end Power circuit: EverLink BTR screw connectors 2 cable(s) 125 mm²flexible with cable end Power circuit: EverLink BTR screw connectors 2 cable(s) 125 mm²flexible with cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 135 mm²solid Power circuit: EverLink BTR screw connectors 2 cable(s) 125 mm²solid |
| Tightening Torque                        | Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 8 N.m - on EverLink BTR screw connectors - cable 2535 mm² hexagonal screw head 4 mm Power circuit: 5 N.m - on EverLink BTR screw connectors - cable 125 mm² hexagonal screw head 4 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2 Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver pozidriv No 2  |

| Operating Time           | 419 ms opening<br>1226 ms closing   |
|--------------------------|---|
| Safety Reliability Level | B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1 |
| Mechanical Durability    | 6 Mcycles   |
| Maximum Operating Rate   | 3600 cyc/h 60 °C  |

# Complementary

| Coil Technology                 | Without built-in suppressor module  |
|---------------------------------|---|
| Control Circuit Voltage Limits  | 0.30.6 Uc (-4070 °C):drop-out AC 50/60 Hz<br>0.81.1 Uc (-4060 °C):operational AC 50 Hz<br>0.851.1 Uc (-4060 °C):operational AC 60 Hz<br>11.1 Uc (6070 °C):operational AC 50/60 Hz |
| Inrush Power In Va              | 140 VA 60 Hz cos phi 0.75 (at 20 °C)<br>160 VA 50 Hz cos phi 0.75 (at 20 °C)  |
| Hold-In Power Consumption In Va | 13 VA 60 Hz cos phi 0.3 (at 20 °C)<br>15 VA 50 Hz cos phi 0.3 (at 20 °C)  |
| Heat Dissipation                | 45 W at 50/60 Hz  |
| Auxiliary Contacts Type         | type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1   |
| Signalling Circuit Frequency    | 25400 Hz  |
| Minimum Switching Current       | 5 mA for signalling circuit   |
| Minimum Switching Voltage       | 17 V for signalling circuit   |
| Non-Overlap Time                | 1.5 ms on de-energisation between NC and NO contact     1.5 ms on energisation between NC and NO contact  |
| Insulation Resistance           | > 10 MOhm for signalling circuit  |

#### **Environment**

| Ip Degree Of Protection               | IP20 front face conforming to IEC 60529  |
|---------------------------------------|--|
| Climatic Withstand                    | conforming to IACS E10 conforming to IEC 60947-1 Annex Q category D  |
| Protective Treatment                  | TH conforming to IEC 60068-2-30  |
| Pollution Degree                      | 3  |
| Ambient Air Temperature For Operation | -4060 °C<br>6070 °C with derating  |
| Ambient Air Temperature For Storage   | -6080 °C   |
| Operating Altitude                    | 03000 m  |
| Fire Resistance                       | 850 °C conforming to IEC 60695-2-1   |
| Flame Retardance                      | V1 conforming to UL 94   |
| Mechanical Robustness                 | Vibrations contactor open: 2 Gn, 5300 Hz<br>Vibrations contactor closed: 4 Gn, 5300 Hz<br>Shocks contactor open: 10 Gn for 11 ms<br>Shocks contactor closed: 15 Gn for 11 ms |
| Height                                | 122 mm   |
| Width                                 | 119 mm   |
| Depth                                 | 120 mm   |
| Net Weight                            | 1.87 kg  |

## **Packing Units**

| Unit Type Of Package 1       | PCE       |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1         |
| Package 1 Height             | 14.000 cm |
| Package 1 Width              | 16.200 cm |
| Package 1 Length             | 19.500 cm |
| Package 1 Weight             | 2.070 kg  |
| Unit Type Of Package 2       | S03       |
| Number Of Units In Package 2 | 4         |
| Package 2 Height             | 30.000 cm |
| Package 2 Width              | 30.000 cm |
| Package 2 Length             | 40.000 cm |
| Package 2 Weight             | 8.747 kg  |

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



#### **Certifications & Standards**


| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Compliant   |
|                          | EU RoHS Declaration   |
| China Rohs Regulation    | China RoHS declaration  |
|                          | Pro-active China RoHS declaration (out of China RoHS legal scope)   |
| Environmental Disclosure | Product Environmental Profile   |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile      | End of Life Information   |

### **Product datasheet**

#### LC2D40AFE7

**Dimensions Drawings** 

#### **Dimensions**



Connections and Schema

Wiring

