# **Product datasheet**

Specifications





# Easy TeSys differential thermal overload relay 2.5...4 A - class 10A

LRE08

#### Main

Range	Easy TeSys
Range Of Product	Easy TeSys Protect
Product Or Component Type	Differential thermal overload relay
Device Short Name	LRE
Relay Application	Motor protection
Phase Failure Sensitivity	Tripping current 130 $\%$ of Ir on two phase, the last one at 0 conforming to IEC 60947-4-1
Colour	Grey (RAL 7011)

## Complementary

j	
Product Compatibility	LC1E0638
Network Type	AC
Network Frequency	5060 Hz
Mounting Support	Under contactor Plate, with specific accessories Rail, with specific accessories
Thermal Overload Class	Class 10A conforming to IEC 60947-4-1
Signalling Function	Relay trip indicator
Thermal Protection Adjustment Range	2.54 A
Tripping Threshold	1.14 +/- 0.06 Ir conforming to IEC 60947-4-1
Mechanical Robustness	Shocks: 6 Gn for 11 ms conforming to IEC 60068-2-7 Vibrations: 3 GN conforming to IEC 60068-2-6
Auxiliary Contact Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	5 A for signalling circuit
[Ue] Rated Operational Voltage	<= 690 V AC
Associated Fuse Rating	10 A gG for power circuit 6 A aM for power circuit 5 A gG for signalling circuit
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947-4-1
[Uimp] Rated Impulse Withstand Voltage	6 kV
Local Signalling	Trip indicator
Control Type	Push-button red stop: Push-button green reset:
Temperature Compensation	-2060 °C

Connections - Terminals	Power circuit: screw clamp terminals 1 1.56 mm <sup>2</sup> - cable stiffness: flexible without cable end		
	Power circuit: screw clamp terminals 1 14 mm <sup>2</sup> - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 1 16 mm <sup>2</sup> - cable stiffness: solid without cable end Signalling circuit: screw clamp terminals 2 12.5 mm <sup>2</sup> - cable stiffness: flexible without cable end Signalling circuit: screw clamp terminals 2 12.5 mm <sup>2</sup> - cable stiffness: flexible with cable end Signalling circuit: screw clamp terminals 2 12.5 mm <sup>2</sup> - cable stiffness: solid without cable end		
		Recommended Tightening Torque	Power circuit: 1.7 N.m - on screw clamp terminals Signalling circuit: 1.7 N.m - on screw clamp terminals
		Height	44.5 mm
		Width	45 mm
		Depth	70 mm
Net Weight	0.13 kg		

#### Environment

Standards	IEC 60947-5-1 IEC 60947-4-1
Product Certifications	EAC
Protective Treatment	TH conforming to IEC 60068
Ip Degree Of Protection	IP20 conforming to IEC 60529
Ambient Air Temperature For Operation	-2060 °C without derating conforming to IEC 60947-4-1 -2070 °C with derating
Ambient Air Temperature For Storage	-6080 °C
Fire Resistance	850 °C conforming to IEC 60068-2-1
Dielectric Strength	6 kV at 50 Hz conforming to IEC 60255-5
Electromagnetic Compatibility	Surge withstand: 6 kV conforming to IEC 60801-5

## **Packing Units**

PCE
1
5.000 cm
8.000 cm
8.400 cm
145.000 g
S02
33
15.000 cm
30.000 cm
40.000 cm
5.118 kg

#### **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information