

rack X80 - 6 slots - Redundant PS - Ethernet backplane



BMEXBP0602H

Main

Range Of Product	Modicon X80	
Accessory / Separate Part Type	Ruggedized rack	
Product Specific Application	For severe environments	

Complementary

Number Of Slots	6 bus X + Ethernet	
Product Compatibility	BMX processor Specific application module BMXCPS4002 BME processor I/O module	
Power Consumption In W	191 mW 3.3 V DC 3.6 W 24 V DC	
Electrical Connection	1 connector (XBE) expansion module	
Fixing Mode	By 4 screws - diameter: 4.326.35 mm, mounting on panel By 4 M6 screws, mounting on plate By clips, mounting on 35 mm symmetrical DIN rail	
Current Consumption	152 mA at 24 V DC 58 mA at 3.3 V DC	
Mtbf Reliability	1353797 H	
Net Weight	1.02 kg	

Environment

19-Apr-2024

Ip Degree Of Protection	IP20	
Ambient Air Temperature For Operation	-2570 °C	
Relative Humidity	595 % without condensation	
Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility 2014/34/EU - ATEX directive	
Product Certifications	CE UL CSA RCM EAC Merchant Navy ATEX zone 2/22	

IECEx zone 2/22

<u> </u>		
Standards	IEC 61131-2	
	IEC 61010-2-201	
	UL 61010-2-201	
	CSA C22.2 No 61010-2-201	
	IACS E10	
	IEC 61000-6-5, interface type 1 and type 2	
	IEC 61850-3, location G	
	IEC 60079-0	
Environmental Characteristic	Gas resistant class Gx conforming to ISA S71.04	
	Gas resistant class 3C4 conforming to IEC 60721-3-3	
	Dust resistant class 3S4 conforming to IEC 60721-3-3	
	Sand resistant class 3S4 conforming to IEC 60721-3-3	
	Salt resistant level 2 conforming to IEC 68252	
	Mold growth resistant class 3B2 conforming to IEC 60721-3-3	
	Fungal spore resistant class 3B2 conforming to IEC 60721-3-3	
	Hazardous location class I division 2	
Protective Treatment	Conformal coating	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	15.500 cm
Package 1 Length	46.000 cm
Package 1 Weight	1.020 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	9
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	10.000 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

BMEXBP0602H

Dimensions Drawings

Dimensions



Dimensions in mm

a Empty Rack	Rack With Extender Module Mounted	b	С
375.80		NOTE: Overall height is 134.6 with a CPU mounted.	19

Dimensions in in.


а			
Empty Rack	Rack With Extender Module Mounted	b	С
14.80	14.84	NOTE: Overall height is 5.30 with a CPU mounted.	0.75

BMEXBP0602H

Mounting and Clearance

Minimum Clearance


Minimum Clearance of a typical installation in a cabinet with ducts




- a Side clearance: > 40 mm (1.57 in.)
- **b** Top and bottom clearance with surrounding objects: > 20 mm (0.79 in.)
- 1 Installation or casing
- 2 Wiring duct or tray

BMEXBP0602H

Mounting a Rack on a DIN rail



Mounting and Fastening the Rack on Panels




NOTE: You can use M4, M5, M6, or UNC #6 screws in the fastening holes.

Dimensions in mm		
а	b	
332.5	345.2	

Dimensions in in.		
а	b	
13.09	13.59	

Mounting on Telequick Grid AM1-PA and AM3-PA Mounting Grids



Fasten the rack with four M4, M5, M6 or UNC #6 screws