Product datasheet

Specification





miniature plug-in relay - Zelio RXM2L - 4 C/O - 24 V DC - 3 A - without LED

RXM4LB1BD

Main

Range Of Product	Harmony Electromechanical Relays	
Coil Interference Suppression	Without	
Series Name	Miniature	
Product Or Component Type	Plug-in relay	
Device Short Name	RXM	
Contacts Type And Composition	4 C/O	
[Ithe] Conventional Enclosed	3 A at -4055 °C	

Complementary

Contact Operation	Standard	
[Uc] Control Circuit Voltage	24 V DC	
Status Led	Without	
Control Type	Without push-button	
[Uimp] Rated Impulse Withstand Voltage	2.5 kV during 1.2/50 µs conforming to IEC 61810-7	
[le] Rated Operational Current	ant 3 A (AC-1/DC-1) NO conforming to IEC 1.5 A (AC-1/DC-1) NC conforming to IEC	
Minimum Switching Capacity	25 mW subject to switching frequency, environment or expected reliability level etc	
Operating Time	20 ms between coil de-energisation and making of the Off-delay contact 20 ms between coil energisation and making of the On-delay contact	
Cad Overall Width	21 mm	
Cad Overall Height	27 mm	
Cad Overall Depth	46 mm	
Minimum Switching Current	5 mA subject to switching frequency, environment or expected reliability level etc	
Minimum Switching Voltage	5 V subject to switching frequency, environment or expected reliability level etc	
Rated Operational Voltage Limits	19.226.4 V DC	
[Ui] Rated Insulation Voltage	250 V conforming to IEC	
Maximum Switching Voltage	250 V AC 28 V DC	
Drop-Out Voltage Threshold	>= 0.1 Uc DC	
Load Current	3 A at 250 V AC 3 A at 28 V DC	
Maximum Switching Capacity	750 VA AC 84 W DC	

Average Resistance	640 Ohm at 23 °C +/- 10 %	
Average Coil Consumption	0.9 W, DC	
Mechanical Durability	10000000 cycles	
Electrical Durability	100000 cycles for resistive load	
Safety Reliability Data	B10d = 100000	
Operating Rate	<= 1200 cycles/hour under load <= 18000 cycles/hour no-load	
Utilisation Coefficient	20 %	
Dielectric Strength	2000 V AC between coil and contact with basic insulation 2000 V AC between poles with basic insulation 1000 V AC between contacts with micro disconnection	
Protection Category	RTI	
Pollution Degree	2	
Operating Position	Any position	
Test Levels	Level A group mounting	
Sale Per Indivisible Quantity	10	
Contacts Material	Silver alloy (Ag/Ni)	
Net Weight	0.033 kg	

Environment

Ip Degree Of Protection	IP40 conforming to IEC 60529
Standards	CE IEC 61810-1 (iss. 2)
Ambient Air Temperature For Storage	-4085 °C
Vibration Resistance	3 gn, amplitude = +/- 1 mm (f = 1050 Hz)operating conforming to IEC 60068-2-6 6 gn, amplitude = +/- 1 mm (f = 1050 Hz)not operating conforming to IEC 60068-2-6
Shock Resistance	30 gn for not operating conforming to IEC 60068-2-27 10 gn for in operation conforming to IEC 60068-2-27

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	2.9 cm
Package 1 Length	4.8 cm
Package 1 Weight	34.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	3.1 cm
Package 2 Width	11.2 cm
Package 2 Length	13.6 cm
Package 2 Weight	361.0 g
Unit Type Of Package 3	S02

Number Of Units In Package 3	270
Package 3 Height	15.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	10.65 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Dimensions Drawings

Dimensions



Pin Side View




RXM4LB1BD

Connections and Schema

Wiring Diagram





Symbols shown in blue correspond to Nema marking.

Product datasheet


RXM4LB1BD

Performance Curves

Electrical Durability of Contacts

Durability (inductive load) = durability (resistive load) x reduction coefficient.

For 4 Poles Relay



X: Contact current (A)

Y: Durability (Number of operating cycles)


A: Inductive load B: Resistive load

Note: These are typical curves, actual durability depends on load, environment, duty cycle, etc.

For inductive load, to increase relay life cycles, please add a proper load protection circuit (eg: RC protection/Varistor/free Wheeling diode -DC load only-)

Maximum Switching Capacity

For 4 Poles Relay



X : Contact voltage (v)

Y: Contact current (A)

A: Inductive AC load

B: Resistive AC load

C: Inductive DC load

D: Resistive DC load

Note: These are typical curves, actual durability depends on load, environment, duty cycle, etc.

For inductive load, to increase relay life cycles, please add a proper load protection circuit (eg: RC protection/Varistor/free Wheeling diode -DC load only-)

For low level loads (below 10mA), we recommend to use RXM*GB series with bifurcated contacts relays instead.