# **Product datasheet**

Specification





# servo motor BMH, Lexium 32, 8.4Nm, 6000rpm, untapped shaft, with brake, IP54, 16bit encoder

BMH1003P06F2A

## Main

Product Or Component Type	Servo motor		
Device Short Name	ВМН		
Maximum Mechanical Speed	6000 rpm		
Continuous Stall Torque	8.4 N.m for LXM32.D30N4 at 10 A, 400 V, three phase 8.4 N.m for LXM32.D30N4 at 10 A, 480 V, three phase		
Peak Stall Torque	25.1 N.m for LXM32.D30N4 at 10 A, 400 V, three phase 25.1 N.m for LXM32.D30N4 at 10 A, 480 V, three phase		
Nominal Output Power	2700 W for LXM32.D30N4 at 10 A, 400 V, three phase 2700 W for LXM32.D30N4 at 10 A, 480 V, three phase		
Nominal Torque	6.2 N.m for LXM32.D30N4 at 10 A, 400 V, three phase 6.2 N.m for LXM32.D30N4 at 10 A, 480 V, three phase		
Nominal Speed	4000 rpm for LXM32.D30N4 at 10 A, 400 V, three phase 4000 rpm for LXM32.D30N4 at 10 A, 480 V, three phase		
Product Compatibility	LXM32.D30N4 at 400480 V three phase		
Shaft End	Smooth shaft		
Ip Degree Of Protection	IP54 standard		
Speed Feedback Resolution	32768 points/turn		
Holding Brake	With		
Mounting Support	International standard flange		
Electrical Connection	ion Rotatable right-angled connectors		

# Complementary

,			
Range Compatibility	Lexium 32		
[Us] Rated Supply Voltage	480 V		
Network Number Of Phases	Three phase		
Continuous Stall Current	7.69 A		
Continuous Power	3.3 W		
Maximum Current Irms	29.1 A for LXM32.D30N4		
Maximum Permanent Current	29.1 A		
Second Shaft	Without second shaft end		
Shaft Diameter	19 mm		
Shaft Length	40 mm		
Feedback Type	Single turn SinCos Hiperface		
Holding Torque	9 N.m holding brake		

Motor Flange Size	100 mm		
Number Of Motor Stacks	3		
Torque Constant	1 N.m/A at 120 °C		
Back Emf Constant	63.5 V/krpm at 120 °C		
Number Of Motor Poles	10		
Rotor Inertia	10.3 kg.cm²		
Stator Resistance	0.63 Ohm at 20 °C		
Stator Inductance	4 mH at 20 °C		
Stator Electrical Time Constant	6.3 ms at 20 °C		
Maximum Radial Force Fr	1050 N at 1000 rpm 830 N at 2000 rpm 730 N at 3000 rpm 660 N at 4000 rpm 610 N at 5000 rpm		
Maximum Axial Force Fa	0.2 x Fr		
Brake Pull-In Power	18 W		
Type Of Cooling	Natural convection		
Length	234.3 mm		
Centring Collar Diameter	95 mm		
Centring Collar Depth	3.5 mm		
Number Of Mounting Holes	4		
Mounting Holes Diameter	9 mm		
Circle Diameter Of The Mounting Holes	115 mm		
Net Weight	8.15 kg		

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19.5 cm
Package 1 Width	22.0 cm
Package 1 Length	40.0 cm
Package 1 Weight	8.6 kg
Unit Type Of Package 2	P06
Number Of Units In Package 2	12
Package 2 Height	77.0 cm
Package 2 Width	80.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	111.7 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>Ø</b>	Mercury Free	
	Rohs Exemption Information	Yes
<b>②</b>	Pvc Free	

#### **Certifications & Standards**


Circularity Profile	No need of specific recycling operations		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
<b>Environmental Disclosure</b>	Product Environmental Profile		
China Rohs Regulation	China RoHS declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
Reach Regulation	REACh Declaration		

## BMH1003P06F2A

#### **Dimensions Drawings**

#### **Servo Motors Dimensions**

#### **Example with Straight Connectors**



- a: Power supply for servo motor brake
- b: Power supply for servo motor encoder
- (1) Shaft end, keyed slot (optional)
- (2) For screw M6 x 21 mm/M6 x 0.83 in.

#### Dimensions in mm

Straight connectors		Rotatable angled connectors		a (with a st bunka)	a (with handes)
b1	b2	b1	b2	c (without brake)	c (with brake)
39.5	25.5	39.5	39.5	192	234

#### Dimensions in in


Straight connectors		Rotatable angled connectors		c (without brake)	( د ا د ا د ا د ا د ا	
b1	b2	b1	b2	c (without brake)	c (with brake)	
1.55	1.00	1.55	1.55	7.55	9.21	

#### Performance Curves

## 400 V 3-Phase Supply Voltage

#### **Torque/Speed Curves**

Servo motor with LXM32•D30N4 servo drive




- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

#### 480 V 3-Phase Supply Voltage

#### **Torque/Speed Curves**

Servo motor with LXM32•D30N4 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque