Product datasheet

Specifications





Controller M100 - 14I/10O relay - 220VAC

TM100C24RN

Main

Range Of Product	Easy Modicon M100
Product Or Component Type	Logic controller
[Us] Rated Supply Voltage	100240 V AC
Discrete I/O Number	24
Discrete Input Number	I2I5: 4 fast input I0I1: 2 high speed input I6I13: 8 regular input
Discrete Output Number	10 relay
Discrete Input Voltage	24 V
Discrete Input Voltage Type	DC
Discrete Input Current	7 mA for regular input 7 mA for fast input 9 mA for high speed input
Discrete Output Voltage	24 V DC 220 V AC
Discrete Output Current	2 A
Discrete Output Type	Relay normally open
Power Consumption In Va	3143 VA at 100240 V AC (with max I/O)

Complementary

Supply Voltage Limits	85264 V
Voltage State 1 Guaranteed	>= 15 V for input
Voltage State 0 Guaranteed	<= 5 V for input
Network Frequency	50/60 Hz
Inrush Current	50 A
Input Impedance	3.3 kOhm for regular input 3.3 kOhm for fast input 2.81 kOhm for high speed input
Response Time	35 μs turn-on, I2I5 terminal(s) for fast input 100 μs turn-off, I2I5 terminal(s) for fast input 5 μs turn-on, I0I1 terminal(s) for high speed input 5 μs turn-off, I0I1 terminal(s) for high speed input 10 ms turn-on, Q0Q9 terminal(s) for relay output 10 ms turn-off, Q0Q9 terminal(s) for relay output 35 μs turn-on, I6I13 terminal(s) for regular input 100 μs turn-off, I6I13 terminal(s) for regular input
Configurable Filtering Time	0 ms for input 3 ms for input 12 ms for input

Output Voltage Limits	30 V DC 250 V AC
Maximum Current Per Output Common	4 A at COM 0 4 A at COM 1 4 A at COM 2
Electrical Durability	4 A at COM 2 100000 cycles AC-12, 240 V, 480 VA, resistive 100000 cycles DC-12, 24 V, 48 W, resistive
Switching Frequency	0.1 Hz with maximum load 5 Hz without maximum load
Mechanical Durability	20000000 cycles for relay output
Minimum Load	10 mA at 5 V DC for relay output
Memory Capacity	1024 kB internal flash with 10000 instructions for backup of programs
Data Storage Equipment	32 GB micro SD card (optional)
Execution Time For 1 Kinstruction	0.3 ms for event and periodic task
Execution Time Per Instruction	0.2 μs Boolean
Exct Time For Event Task	60 µs response time
Regulation Loop	Adjustable PID regulator up to 14 simultaneous loops
Control Signal Type	Quadrature (x1, x2, x4) at 60 kHz for fast input (HSC mode) Pulse/direction at 60 kHz for fast input (HSC mode) Single phase at 60 kHz for fast input (HSC mode) CW/CCW at 60 kHz for fast input (HSC mode)
Counting Input Number	2 fast input (HSC mode) at 60 kHz 32 bits
Integrated Connection Type	USB port with mini B USB 2.0 connector Non isolated serial link serial 1 with terminal block connector and RS485 interface Non isolated serial link serial 2 with terminal block connector and RS232/RS485 interface
Transmission Rate	1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485 1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232 12 Mbit/s for USB
Communication Port Protocol	USB port: USB - SoMachine-Network Non isolated serial link: Modbus master/slave - RTU/ASCII or SoMachine-Network
Local Signalling	1 LED (green) for PWR 1 LED (green) for RUN 1 LED (red) for module error (ERR) 1 LED (green) for SD card access (SD) 1 LED (green) for SL1 1 LED per channel (green) for I/O state
Electrical Connection	removable screw terminal blockfor inputs removable screw terminal blockfor outputs removable screw terminal block, 4 terminal(s) for connecting the serial link1 Mini B USB 2.0 connectorfor a programming terminal removable screw terminal block, 3 terminal(s) for connecting the 100-240 V AC power supply
Maximum Cable Distance Between Devices	Shielded cable: <10 m for fast input Shielded cable: <10 m for high speed input Unshielded cable: <150 m for output Unshielded cable: <50 m for regular input
Insulation	Between input and internal logic at 560 V AC Between fast input and internal logic at 560 V AC Between input groups at 560 V AC Non-insulated between inputs Between output and internal logic at 1780 V AC Between output groups at 1780 V AC Between supply and internal logic at 1780 V AC
Sensor Power Supply	24 V DC
Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 plate or panel with fixing kit conforming to IEC 60715

Height	90 mm
Depth	70 mm
Width	130 mm
Net Weight	0.351 kg

Environment

lp Degree Of Protection	IP20 with protective cover in place
Product Certifications	CE
Standards	EN/IEC 61010-2-201 EN/IEC 61131-2
Electromagnetic Compatibility	Electrostatic discharge immunity test - test level: 8 kV (air discharge) conforming to EN/IEC 61000-4-2
	Electrostatic discharge immunity test - test level: 6 kV (contact discharge) conforming to EN/IEC 61000-4-2
	Susceptibility to electromagnetic fields - test level: 10 V/m (80 MHz3 GHz) conforming to EN/IEC 61000-4-3
	Conducted emission - test level: 79 dBµV/m QP/66 dBµV/m AV (power lines (AC)) conforming to EN/IEC 55011
	Conducted emission - test level: 73 dBµV/m QP/60 dBµV/m AV (power lines (AC)) conforming to EN/IEC 55011
	Radiated emission - test level: 40 dB μ V/m QP class A (10 m) conforming to EN/IEC 55011
	Radiated emission - test level: 47 dBμV/m QP class A (10 m) conforming to EN/IEC 55011
	Magnetic field at power frequency - test level: 30 A/m (I/O) conforming to EN/IEC 61000-4-8
	Electrical fast transient/burst immunity test - test level: 2 kV (power lines) conforming to EN/IEC 61000-4-4
	Electrical fast transient/burst immunity test - test level: 2 kV (relay output) conforming to EN/IEC 61000-4-4
	Electrical fast transient/burst immunity test - test level: 1 kV (I/O) conforming to EN/ IEC 61000-4-4
	Electrical fast transient/burst immunity test - test level: 1 kV (serial link) conforming to EN/IEC 61000-4-4
	1.2/50 μs shock waves immunity test - test level: 1 kV (power lines (DC)) conforming to EN/IEC 61000-4-5
	1.2/50 μs shock waves immunity test - test level: 2 kV (power lines (AC)) conforming to EN/IEC 61000-4-5
	1.2/50 μs shock waves immunity test - test level: 2 kV (relay output) conforming to EN/IEC 61000-4-5
	1.2/50 μs shock waves immunity test - test level: 1 kV (I/O) conforming to EN/IEC 61000-4-5
	$1.2/50\ \mu s$ shock waves immunity test - test level: 1 kV (shielded cable) conforming to EN/IEC 61000-4-5
	1.2/50 μs shock waves immunity test - test level: 0.5 kV class A (power lines (DC)) conforming to EN/IEC 61000-4-5
	1.2/50 μs shock waves immunity test - test level: 1 kV class A (power lines (AC)) conforming to EN/IEC 61000-4-5
	1.2/50 µs shock waves immunity test - test level: 1 kV (relay output) conforming to EN/IEC 61000-4-5
	Conducted RF disturbances - test level: 10 V (0.1580 MHz) conforming to EN/IEC 61000-4-6
Shock Resistance	15 gn for 11 ms 30 gn for 6 ms
mmunity To Microbreaks	10 ms
Vibration Resistance	3.5 mm at 5…8.4 Hz on symmetrical rail 1 gn at 8.4…150 Hz on symmetrical rail
	3.5 mm at 58.4 Hz on panel mounting
	3 gn at 8.4…150 Hz on panel mounting
Relative Humidity	1095 %, without condensation (in operation) 1095 %, without condensation (in storage)
Ambient Air Temperature For Operation	055 °C (horizontal installation)
	-2570 °C
Ambient Air Temperature For Storage	-2570 C

Operating Altitude	02000 m
Storage Altitude	03000 m

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.466 cm
Package 1 Width	13.681 cm
Package 1 Length	14.27 cm
Package 1 Weight	545.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	7.04 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	288
Package 3 Height	95.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	177.96 kg

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Product datasheet

Dimensions Drawings

Dimensions Drawings

Dimensions

